HINGES

**3-WAY ADJUSTABLE** 

**CONCEALED HINGES** 

## **3-WAY ADJUSTABLE CONCEALED HINGE** For Door Moldings







## HES3D-W190




- · Has a long arm for a wider throw, allowing 3/8" (10 mm) clearance for flush installation or 1/2" (13 mm) clearance for installation with a molding. Opens to 180°.
- Features 3-way adjustability (vertical, horizontal and depth).
- UL Rated, up to 3 Hours (DC, DN, and BL models only)
- Flanges come apart for the door to be provisionally hung for making adjustments. This provides a quick and easy installation when ready for fixing screws.
- Successfully passed 300,000 open/ close private cycle tests
- Replacement screw covers available for all finishes.
- Only the HES3D-W190PN model includes metal cover plates\*, all other models include plastic cover plates.

Horizonta





120 Frame
90°
60°
Door 1-7/16" (36 mm)
1-3/4" (45 mm)
The example drawing shows the case that there is a step of 10 mm between the door and the frame.



					4	<b>t</b>				
Select models only										
No.	Part Name	Material	Finish/Color							
140.	Fait Name Iviaterial		DC	DN	BL	PN	WT	PB		
1	Body	Zinc Alloy (ZDC)			Enamel		Enamel			
2	Base Frame	Zilic Alloy (ZDC)	Satin	Nickel	Black	Nickel	White	Brass		
3	Arm	Aluminium Allloy			DIACK		vviille			
4	Shaft	Stainless Steel	Plain	Plain	Plain	Plain	Plain	Plain		

5 Screw Cover ABS/Stainless Steel\* Silver Dull Nickel Black Nickel White Brass


Item Name	Finish	Door Size		Door Weight		Opening	Weight	Box	Carton	
item Name	FILISH	Width	Height	Thickness	2 pcs	3 pcs	Angle	Weight (g)	(pcs)	(pcs)
HES3D-W190DC-UL	Dull Chrome	Max. - 36" (915 mm)		Min. 1-5/8" (42 mm)	1-5/8" 220 lbs		180°	-	2	12
HES3D-W190DN-UL	Dull Nickel								2	12
HES3D-W190BL-UL	Black		Max. 96-1/16"						2	12
HES3D-W190PN	Polished Nickel		(2440 mm)						2	12
HES3D-W190WT	White								2	12
HES3D-W190PB	Polished Brass								2	12




## 3-WAY ADJUSTABLE CONCEALED HINGE For Cladded Doors









Y	В	X	A	X-Y+1
Door Clearance	Door Chamfering	Frame Clearance	Frame Chamfering	Step Amount
	0	3 to 12	0	1 to 10
3		13	1	11
3		14	2	12
		15	4	13
		3 to 10	0	0 to 7
	1	11	1	8
4		12	2	9
		13	3	10
		14	4	11
	2	3 to 6	0	-1 to 2
		7	1	3
		8	2	4
5		9	3	5
5		10	4	6
	3	11	4	7
		12	5	8
		13	6	9

Υ	В	X	A	X-Y+1
Door Clearance	Door Chamfering	Frame Clearance	Frame Chamfering	Step Amount
	3	3 to 6	0	-2 to 1
		7	1	2
		8	2	3
6	4	9	3	4
		10	4	5
		11	5	6
		12	6	7
	5	3 to 6	0	-3 to 0
		7	1	1
7		8	2	2
,		9	3	3
		10	5	4
		11	7	5
	6	3 to 6	0	-4 to -1
		7	1	0
8		8	3	1
		9	5	2
		10	7	3