


ULTRA THIN & STRONG MAGNETIC CATCH







MC-158, MC-159



· Unique ultra thin magnetic catch design with extra strong magnetic force.

Note: 1) Max. temperature: 80°C (176°F)

- 2) To avoid breakage, counterplate should not hit magnet.
- 3) Screw heads should not protrude above the base plate.
- 4) Screws not included, use M3 flat head or equivalent.
- 5) Counterplate MC-159-Plate sold separately.

Counterplate-Optional			30 → 1.6
			\$ \frac{1}{2} \text{\$\frac{1}{2} \text{\$\frac{1} \text{\$\frac{1} \text{\$\frac{1} \text{\$\frac{1} \text{\$\frac{1} \$\frac{1
Item No.	Material	Finish	2 - Ø4.2 Ø6.2
MC-159-Plate	Steel	Nickel	(5/8")

Item No.	Magnetic Force (kg)	Weight (g)	Box (pcs)	Carton (pcs)
MC-158	1.5 (3.3 lbs)	12	200	1000
MC-159, MC-159/BL	4.0 (8.8 lbs)	12	200	1000

Part Name	Material	Finish	
Magnet	Neodymium	Nickel/ Black (MC-159 only)	
Base/Yoke	Steel		


ULTRA THIN MAGNETIC CATCH








MC-YN001P



· Strong magnetic force.

Note: 1) Max. temperature: 80°C (176°F)

- 2) To avoid breakage, counterplate should not hit magnet.
- 3) Screw heads should not protrude above the base plate.



R7.5	35 (1-3/8") 25 (1")	Ø4.6,Ø7
=	90°	
ne .	Mate	rial

Item No.	Magnetic Force (kg)	Weight (g)	Box (pcs)	Carton (pcs)
MC-YN001P	2.7 (5.9 lbs)	7.5	100	1000

Part Name	Material	Finish	
Magnet	Neodymium	Nickel	
Base/Yoke/Counterplate	Steel	INICKEI	

ULTRA THIN STAINLESS STEEL MAGNETIC CATCH








MC-YN015SP



- Ultra-thin magnetic catch with strong rare-earth (neodymium) magnet.
- · 304 stainless steel yoke for high corrosion resistance.
- · Magnetic catch includes self-tapping screws.
- Note: 1) Magnetic force may be affected when used in/around water or high humidity.
 - 2) Max. recommended temperature: 80°C (176°F).
 - 3) Counterplate should not come into direct contact with magnet when closing.
 - 4) Screw heads should not protrude above the base plate.



No.	Part Name		Material		Finish		
1	Main Body		Stainless Steel		Plain		
2	Yoke		304 Stainless Steel		7	Fidili	
3	Magnet		Neodymium		Epoxy Coating		
4	Counterplate		Stainless Steel		Р	Plain	
Item No.		Magnetic Fo	rce (kg)	Weight (g)	Box (pcs)	Carton (pcs)	
MC-YN015SP 2		2.3 kg (5	0 lbs)	7.3	100	2000	