
**CATCHES & LATCHES** 



### **NON-MAGNETIC MINI TOUCH LATCH**




### NS-2



# **NON-MAGNETIC MINI TOUCH LATCH**




#### PR-4PK



	PR4PKB/STRIKE1 (Strike for wood)	(5)	7.7.
PR4PKB/STRI (Strike for meta			-10-
ote: Strikes sold separately.		3.5	PR4PKB/STR <b>I</b> KE2

•	Pusn to	latch/uni	atcn.
	N # ! ! - 4		1-1-1-

- · Miniature design is ideal for small applications.
- Snap-in style catch.
- Strike sold separately.



Part Name	Material	Color	
Body	Polyacetal	Black	
Strike	Polyamide		

## **NON-MAGNETIC MINI TOUCH LATCH**

Weight (g)

0.7



## ESN-195-3.1



Holding Force (kg)


1.2 (2.6 lbs)

Note: Strike sold separately.

Item No.

PR-4PK

Strike isn't rated for UL-94 V0 flame retardant material.



Box (pcs)


1000


Carton (pcs)

8000

Item No.	Retaining Force (kg)	Weight (g)	Box (pcs)
ESN-195-3.1	3.5 (7.7 lbs)	2.3	5000

- · Push to latch/unlatch. · Strong retaining force.
- · Miniature design is ideal for small applications.
- · Snap-in style catch.
- · Strike sold separately.
- · UL-94 V0 rated flame retardant material.





Cut Out Dimensions

Part Name	Material	Finish/Color	
Body	Polybutylene Terephthalate	Black	
Catch	Liquid Crystal Polymer		
Spring	Steel	Chromate	
Slide Catch	Polyamide	Black	
Spring	Steel		