**CATCHES & LATCHES** 



## **CLEAN ROOM DRAW LATCH**






## STF-CV150



Item No. STF-CV150

STF-CV150M



		(= 0,0= )	(4-7)
		(37)	(12)
-25- (63/64' -(1-37/64	3-0 5.3 0 10.5	(1-21/32*)	98 9 3
Load Capacity (kg)	Weight (g)	Finish	

Satin

Mirror

(6-19/64") +1	(27)	3
<u>+</u>	U	No.
		1
		2

- · No metal-to-metal contact. · Ideal for clean room, semiconductor, and food industry applications.
- When used in combination with the TF40C counter plate (below), will have 330 kg load capacity.



No.	Part Name	Material	
1	Handle	316 Stainless Steel	
2	Hook	SCS14 Stainless Steel (Similar to SUS316)	
3	Base	316 Stainless Steel	
4	Hook Screw   SCS14 Stainless Steel (Similar to S		
⑤	Handle Cover	Polypropylene	

## **HEAVY DUTY COUNTERPLATE**

248



draw latch.




• Heavy duty center plate for STF-CV150 clean room

TF-40C



330 (727 lbs)

TF40C-ST



Item No.	Weight (g)	Box (pcs)	Carton (pcs)	Material	Finish
TF-40C-ST	48	5	20	SCS14 Stainless Steel (Similar to SUS316)	Satin
TF-40C-STM					Mirror

## **CLEAN ROOM MAGNETIC CATCHES** MC-JM45 MC-JMP45 (See P.108 for details) (See P.104 for details) MC-JM63G (See P.104 for details)

