

SLIDING DOOR LATCH




HC-3051 SERIES




- · Recessed latch handle for wooden sliding doors.
- 4 model types available.
- The backset can be installed at any position between 30 mm and 51 mm from the door edge.
- Applicable door thickness: 35-45 mm (1-3/8"~1-3/4"). 3 different lengths of spindles and 2 different lengths of screw are included. Initial setting is for 38 mm door.
- For residential interior sliding doors, including pocket doors.

■ Latch Body & Strikeplate







■ Latch Faceplates



The opposite face of every model has a slide handle, as shown for the DSL model.



Double sided slide latch (DSL)

■ Parts Included


- -Spindles Ø4×35, Ø4×39, Ø4×43
- -Countersunk head tapping screw 3.5×25 (SUS) for strike & latch body
- -Countersunk head screw M4×20, M4×25 (SUS) for latch face plates.

Item Name	Туре	Weight (g)	Box (pcs)	Carton (pcs)
HC-3051-PRV-NI	Privacy	531		20
HC-3051-IND-NI	Privacy w/ Indicator	535	1	
HC-3051-CLD-NI	Cylinder lock	557	I	
HC-3051-DSL-NI	Double Sided Slide	511		




HC-3051-CLD-NI is shown






■ Cut Out Dimensions



■ Adjustment to the strikeplate




- Vertical adjustment Loosen screw A and adjust the back side case. And then re-fasten screw A.
- Horizontal adjustment Loosen screw B and adjust the gap between door and door frame.





Misalignment if screw B is loosened too much.

■ Checking the operation of latch



No.	Part Name	Material	Finish
1	Base	Zinc Alloy	Nickel
2	Knob	Zilic Alloy	
3	Latch Body	Steel	Plain
4	Spindle	Steel	
(5)	Trigger		Polished
6	Bolt	304 Stainless Steel	Polished
7	Front Plate (Latch)		Satin
8	Strike	Steel	Plain
9	Front Plate (Strike)	304 Stainless Steel	Stain