LOCKS



## **CABINET LOCK (W/INDICATOR)**


















Installation for drawer

Installation for right-handed door (This application is available with special ordered lock.)

- Only 1/8 turn is needed to unlock/lock the door.
  Key automatically returns to original position, making it easy to remove the key.
- With indicator.
- 300 key changes available; Please specify keyed alike or differently when ordering.
- Master key type available at surcharge.
- (Maximum 170 key changes per master key)
- · Keys can be shared with other 2200 series locks.



	Item No.		Door Thickness		Weight (g)	Box (pcs)		Carton (pcs)
	2200QL-24		24 (15/16")		200	12		60
i	No. Part Name				Material		Finish	
	INU.						_	
	1	Body		03	304 Stainless Steel		Plain	
	2	Cylinder (Outer)			Brass		Satin Nickel	
	3	Cyli	inder (Inner)	Zinc Alloy Brass				
	4		Dead Bolt			Nickel		
	(5)		Key					

## Open Automatic Return Close

Operation


## STAINLESS STEEL CABINET LOCK







3810S








- Components made of 304 stainless steel for corrosion resistance.
- Durable key made of corrosion/abrasion resistant nickel. Key is reversible.
- Cylinder rotates for either drawer or cabinet door application.
- Up to 300 key changes available. Please specify keyed alike or differently when ordering.
- Master key option available as a special order at a surcharge.
- Can be used with spacer 6810-SP (P.623), sold separately.



<del>---</del>12 (15/32")



To change lock for drawer application, turn cylinder 90° counterclockwise and install fixing screw.

Item No.	L	Door Thickness (mm)	Weight (g)	Box (pcs)	Carton (pcs)
3810S-24	24 ( 15/16" )	24 ( 15/16" )	180	12	60
3810S-30	30 (1-3/16")	30 (1-3/16")	195	12	

NO.	Part Name	Material	Finish
1	Body*		Plain
2	Cylinder Housing	304 Stainless Steel	Satin
3	Dead Bolt		Plain
4	Key	Nickel Silver	

<sup>\*</sup>Cylinder pins are made of brass.