LOCKS




## **PUSH LOCK**





## 2100B






- Push cylinder to lock.
- Cylinder Diameter: 18.6 mm (47/64")
- Keys can be shared with other 2100 series locks.
- 12 key changes available; Please specify keyed alike or differently when ordering.







No.	Part Name	Material	Finish		
1	Body	Zinc Alloy	Satin Nickel		
2	Key	Brass	Nickel		


Item No.	Metal Frame Thickness	Cylinder Diameter	Key Changes	Keys Included	Weight (g)	Box (pcs)	Carton (pcs)
2100B	20 ( 25/32" )	18.6 ( 47/64" )	12	2	50	40	400

## **PUSH LOCK**




2110B





- Zinc alloy cylinder push lock for metal-framed glass doors or sheet metal double sliding doors.
- Key is required to lock and to unlock.
  To Lock: Insert key and turn 60° clockwise. Push-in the cylinder and turn the key 60°
- Cylinder Diameter: 18.6 mm (47/64")
- Keys can be shared with other 2100 series
- 12 key changes available; Please specify keyed alike or differently when ordering.



No.	Part Name	Material	Finish
1	Body	Zinc Alloy	Satin Nickel
2	Key	Brass	Nickel

Item No.	Metal Frame Thickness	Cylinder Diameter	Key Changes	Keys Included	Weight (g)	Box (pcs)	Carton (pcs)
2110B	20 ( 25/32" )	18.6 ( 47/64" )	12	2	50	40	400