

POWER ASSIST HINGE (OUTSIDE MOUNT)



than conventional lift-assist hinges.

• External surface mounted. • Torque adjustable (±10%).

semiconductor equipment.

· Soft closing.


· Mitigates effort needed to lift heavy lids and doors. · Balance adjustment allows for use in a wider range of lids

• Features durable plastic cover for clean appearance. Applications: Medical equipment, analytical instruments,

HG-PA300-15




Balance Adjustment




Angle of peak torque is adjustable with hex key 5 mm (13/64"). This feature allows for position adjustment to change the center of gravity.

(5







Working range





Torque Adjustment






Installation Example







N	n.T	Part Name	Material	Finish	
(1	-	Base A	matorial	1	
(2		Base B	430	-	
(3	3)	Case	Stainless Steel		
(4	9	Link Arm			
E	5)	Plastic Cover	PBT Plastic	Light Grey	
(6	9)	Slider	Polyacetal	-	
(7	0	Spring	Steel	-	
_					

Item No.	Peak Torque Angle	Torque per piece	Weight (g)	Box (pcs)	Carton (pcs)
HG-PA300-15	60° - 80°	133±10 % lbs·in (153±10% kgf·cm)	3400	1	-

3-59/64" (99.5 mm)

1-51/64" (45.5 mm)

1-51/64"