

MAGNETIC CATCH (W/SWITCH)










- Reed switch built-into magnetic catch allows long-term, trouble free service.
- Designed to detect when a door is closed or open.
- Use provided counter plate when stationary part is non-magnetic material. (aluminum, wood, glass etc.).
- SMC-103A. When the plate is in contact with the catch the circuit is open.
 When the plate is removed from catch the circuit is closed.
- SMC-101/103B. When the plate is in contact with the catch the circuit is closed. When the plate is removed from the catch the circuit is opened.
- Special design provides screw mounting options in 2 diffrent orientations.



| Max. Wattage | 10 W |
|------------------------------|---------------------|
| Max. Load Rating | 0.5 A DC |
| Max. Input Voltage | 100V DC |
| Max. Electric Resistance | 0.15Ω |
| Operating Temperature | 0 ~ 60°C (32~140°F) |
| Wire | UL1007 AWG#26 |
| Tensile Strength (Lead wire) | Max. 1kg (2.2 lbs) |
| | |

| Item No. | Туре | Magnetic Force (kg) | Weight (g) | Box (pcs) | Carton (pcs) |
|----------|------|---------------------|------------|-----------|--------------|
| SMC-101B | В | 1 (2.2 lbs) | | | |
| SMC-103A | Α | 2 (C C lba) | 28 | 50 | 200 |
| SMC-103B | В | 3 (6.6 lbs) | | | |


| Ī | No. | Part Name | Material | Finish/Color | |
|---|-----|--------------|---------------|--------------|--|
| ĺ | 1 | Housing | Polycarbonate | Black | |
| Ī | 2 | Counterplate | Steel | Nickel | |
| ı | 3 | Backplate | Steel | | |
| ı | 4 | Magnet | Ferrite | - | |

SEALED MAGNETIC CATCH (W/SWITCH)



MC-JM74SW-30





- Reed switch built-into magnetic catch allows longterm, trouble free service.
- Designed to detect when a door is closed or open.
- IP67 Water-proof.
- PSE Standard.
- Special design provides screw mounting options in 2 different orientations.

| NC (Red) | NO (Blue) | COM (Black) | |
|-------------|--------------|----------------|--|
| г | | | |

| | No. | Part Name | l V | 1aterial | Finish/Color | |
|---|-----|--------------|----------------|----------|--------------|--|
| Ī | 1 | Housing | Polycarbonate | | Black | |
| Ī | 2 | Counterplate | SUS/Polyacetal | | Plain/Black | |
| | 3 | Magnet | Ferrite | | - | |
| 1 | | | | | | |
| ı | | | | AC250V5A | | |

| Rated Voltage | AC250V5A |
|-----------------------|----------------------|
| | AC125V5A |
| | DC30V5A |
| Insulation Resistance | MIN. 100MΩ (DC500V) |
| Contact Resistance | MAX. 100MΩ |
| Contact Rating | DC5V 16mA |
| Operating Temperature | -40°C~80°C. Max60%RH |

| Item No. | Magnetic Force (kg) | Weight (g) | Box (pcs) | Carton (pcs) |
|--------------|---------------------|------------|-----------|--------------|
| MC-JM74SW-30 | 3 (6.6 lbs) | 80 | 10 | 80 |

