
LOCKS




## SHEET METAL CAM LOCK


## **NAL**




- Brass cylinder tubular cam lock.
- 90 degree cam rotation.Key is removable in locked position only. (Key can be used as knob in unlocked position.)
- Please specify key no. or combination when ordering if neccessary.
- 5,000 key changes available. Please specify keyed alike or keyed differently when ordering.



Cut Out Dimensions





No.	Part Name	Material	Finish		
1	Body	Brass	Chrome		
2	Key		Nickel		
3	Cam	Steel			
4	Hex Nut	Steel	Yellow Zinc Chromate		
(5)	nex ivut				

Item No.	Door Thickness	Cylinder Diameter	Key Changes	Keys Included	Weight (g)	Box (pcs)	Carton (pcs)
NAL	Less Than 10 (25/64")	19.0 (3/4") / Width 15.8 (5/8")	5000	2	55	100	300

## SHEET METAL MINI CAM LOCK



## **NAL-S**





One slot type NAL-S-1



Two slot type NAL-S-2

Turn the cam (3) over to use NAL-S as a counterclockwise turn lock.

- Mini zinc alloy cylinder cam lock for sheet metal doors.
- 90 degrees cam rotation.
- Cam is reversible.
- NAL-S-1: Key withdrawals in locked position only. (Key works as a knob in unlocked position.)
- NAL-S-2: Key withdrawals in both locked and unlocked positions.
- Keyed differently is available. (special order only)
  \* Cam should be horizontal when unlocked.
- \* Not suitable for compression latch situation.
- \* Pressure to cam may cause damage to cylinder.
- 100 key changes available.



**Cut Out Dimensions** 

10.5 (13/32") 4 - (1.6) (3)	-	to use NAL-S a counterclockwise tu
3 9: M12 × 1 M3 × 0.5 M3 × 0.5	10.7 55	6

No.	Part Name	Material	Finish	
1	Body	Zinc Alloy	Chrome	
2	Hex Nut		Nickel	
3	Cam	Steel	Zinc	
4	Screw			
(5)	Key		Nickel	
6	Key Ring	Steel		

Item No.	Number of Slot (s)	Cylinder Diameter	Key Changes	Keys Included	Weight (g)	Box (pcs)	Carton (pcs)
NAL-S-1	1	12.0 (15/32") / Width 10.7 (27/64")	100	2	25	100	500
NAL-S-2	2	12.0 (15/32 )/ Width 10.7 (27/64 )					