




Hooks.

Hooks • Latch Hooks • Swing Hooks • Hanger Plates • Recessed Hooks
Magnet Hooks • Coat Hooks • PXB Hook Series • Retractable Hooks







Zwei L HOOKS

Picture	Item No.	Load Capacity (lbs)	Page
	ZL-2101	81	683
	ZL-2102	66	683
	ZL-2103	-	684
	ZL-2104	36~107	684
	ZL-2105	33	685
	ZL-3401	45~90	685

LARGE HOOKS

Picture	Item No.	Load Capacity (lbs)	Page
	JF-45, 70, 110	22~26	686
	JF-50, 80, 120	26~48	686
	JFT-180, 260	22~33	687
	XL-CUJ	30~42	687
	XL-CUF	33~70	687
	XL-SB210	Upper Hook: 44 lbs Lower Hook: 83 lbs	688
	XL-SF115	83	688

SMALL HOOKS

Picture	Item No.	Load Capacity (lbs)	Page
	DS-H-50, 60	22	6829
	KB-H-35, 40	44	689
	KB-H-L		705
	TA-3	35	689
	XL-HJT	17.6~22	690
	HJT	17.6~22	690
	EU	44~66	690
	EL-25, 30	44	691

SMALL HOOKS

Picture	Item No.	Load Capacity (lbs)	Page
	EP-25, 40	44	691
	FC-50, 65	22~26	691
	RN-50	20	692
	RI-074	11	692
	RB-102	-	692
	HJ	17.6~22	693
	HK-CS30	22.4	705
	2H	13.2~22	693
	HJU	17.6~22	693
	4HJU-40M	33.7	694
	5HJU-60M	44.9	694
	KB-F-70	-	695
	KB-F-75	-	695
	TY	6.6~17.6	696
	TF	6.6~26	696
	TL	11~26	696
	PF	4.4	697
	CH	11~17.6	697

LATCH HOOKS

Picture	Item No.	Load Capacity (lbs)	Page
	EN-R100F	132	698
	EN-R80-K	44	698
	EN-K	44~132	699
	EN-R80	44	699
	WH	33	699

SWING HOOKS

Picture	Item No.	Load Capacity (lbs)	Page
	JF-T	22	700
	JN-T100	88	700
	HK-TS, HK-TT	22.5-58.4	701
	TK, TKF	17~26	702
	TZ-360	6.6~13.2	702
	DZ-270	6.6~17.6	702
	RF-D35	11.7~23.4	703
	RF-U50	13	703
	RF-50	6.6	703
	XL-JSF40TT	110	704
	UC	12~14	704
	UJ	14~19	704

HANGER PLATES

Picture	Item No.	Load Capacity (lbs)	Page
	AP	22	706
	SP	22	706

RECESSED HOOKS

Picture	Item No.	Load Capacity (lbs)	Page
	NF-60	44	707
	NF-60D	66	707
	NF-45D	21	708
	NF-60DF	66	709
	HK-CH35	10	710
	NF-K	44	711
	NF-R52, R64, R77	44	712

VANITY HOOKS / MAGNET HOOKS


Picture	Item No.	Load Capacity (lbs)	Page
	SSF	12.8	713
	MJ-45	4.4	713

COAT HOOKS

Picture	Item No.	Load Capacity (lbs)	Page
	DSH-01	22	714
	DSH-04	22	714
	DSH-05	22	714
	DSH-02	22	715
	DSH-03	22	715
	DSH-129	22	716
	DSH-P5	22	716
	EW-65E	44	716

RECESSED HOOKS


Picture	Item No.	Load Capacity (lbs)	Page
	PXB-GR05-111	22	717
	PXB-GR05-211	22	717
	PXB-GR05-212	22.4	718
	PXB-GN05-101	9	719
	PXB-GN05M-101 (mag)	2.4	719
	PXB-GN05-111	18	720
	PXB-WM05-111	22	720
	PXB-UM05-101	22	721
	PXB-UM05-101-Q1	22	721
	PXB-AB05	22	722
	PXB-AC05-111	44	722
	PXB-AS05-111	19.8	723
	PXB-LE05-111	25	723
	PXB-BN05	18.7~ 33	724
	PXB-BNS05	33	725
	PXB-QC05-101	18~33.7	726
	PXB-QC05-111	22.4	726
	PXB-QL05-111	22.5	727
	PXB-WC05-111	22.5	727
	HK-FH	22~33	728
	HK-LB	33.7	728


Zwei L®
Zwei L

Zwei L Hook ZL-2101



- Supplied with stainless steel wood screws (4.1 × 32) and concrete anchor (for wood screw 4.1, ø6 mm hole).




Item No.	Material	Finish/Color	Load Capacity	Weight (g)	Box (pcs)
ZL-2101	316 Stainless Steel	Zwei L	81 lbs (37 kg)	381	1

Zwei L Hook ZL-2102



- Supplied with stainless steel wood screws (4.1 × 32) and concrete anchor (for wood screw 4.1, ø6 mm hole).




Item No.	Material	Finish/Color	Load Capacity	Weight (g)	Box (pcs)
ZL-2102	316 Stainless Steel	Zwei L	66 lbs (30 kg)	221	1

Zwei L Hook ZL-2103



- Supplied with stainless steel wood screws (4.1 × 32), anchor plug and 3 mm allen key.




Item No.	Weight (g)	Box (pcs)
ZL-2103	841	1

No.	Part Name	Material	Finish/Color
①	Hook	316 Stainless Steel	Zwei L
②	Cover		
③	Pin		
④	Base Plate		Plain
⑤	Cap	Silicone Rubber	Clear
⑥	Screws	316 Stainless Steel	Plain

Zwei L Hook ZL-2104



- Supplied with stainless steel wood screw (4.1 × 32).



Part Name	Material	Finish/Color
Body	316 Stainless Steel	Zwei L


Item No.	A	B	C	P_1	P_2	Load Capacity	Weight (g)	Box (pcs)
ZL-2104-10	3/8" (10)	1-1/8" (29)	1-1/8"(29)	3/16" (5)	1/4" (7)	36 lbs (16.3 kg)	61	1
ZL-2104-16	5/8" (16)	1-7/8" (47)	1-7/8" (47)	1/4" (8)	3/8" (10)	107 lbs (48.4 kg)	63	1

()units in mm

Zwei L Hook ZL-2105



• Supplied with stainless steel wood screws (4 × 50).




Item No.	Material	Finish/Color	Load Capacity (kg)
ZL-2105	316 Stainless Steel	Zwei L	15 (33 lbs)

Zwei L Hook ZL-3401



• Supplied with stainless steel wood screws (4 × 30).



ZL-3401-10

ZL-3401-16
ZL-3401-25

Item No.	Material	Finish Color	A	B	C	D	E	F	t	t1	Load Capacity (kg)
ZL-3401-10	316 Stainless Steel	Zwei L	1-7/16" (36.7)	2-3/8" (60)	1-7/16" (37)	15/16" (24.5)	90°	3/8" (10)	1/8" (3.8)	1/4" (6)	45 lbs (20.4)
ZL-3401-16			2-1/4" (58)	3-11/16" (93)	2-1/16" (52)	1-5/8" (41.0)	120°	5/8" (6)	1/8" (3.8)	3/8" (10)	67 lbs (30.6)
ZL-3401-25			3-9/16" (91)	5-11/16" (145)	3-1/8" (80)	2-9/16" (65.0)		1" (25)	1/4" (6.0)	5/8" (16)	90 lbs (40.8)


()units in mm

LARGE UTILITY HOOK

NSF COMPONENT | RoHS | STAINLESS 303 STEEL | LOAD CAPACITY 10~12 kg 22~26 lbs | TEST 4 P.696 | STAINLESS

JF-45, 70, 110





Material	Finish
303 Stainless Steel	Mirror

Item No.	D	W	W1	H	H1	C	C1	t	t1	d1	d2	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Screw
JF-45	1-3/4" (45)	1/2" (12)	3/8" (10)	2-13/16" (72)	1-5/16" (34)	13/16" (20)	5/16" (8.5)	1/8" (3.5)	3/16" (5)	1/8" (3.8)	1/4" (7.2)	22 lbs (10 kg)	40	20	120	3.5 × 16
JF-70	2-11/16" (68)	5/8" (16)	1/2" (13)	4-3/4" (120)	2-3/16" (55)	1-3/8" (35)	9/16" (15.0)	3/16" (4.0)	1/4" (6)	3/16" (4.3)	5/16" (8.6)		95	6	36	4.1 × 20
JF-110	4-5/16" (110)	11/16" (18)	9/16" (14)	7-7/8" (200)	3- 9/16" (90)	2-3/4" (70)	11/16" (17.0)	1/4" (5.5)	5/16" (8)	3/16" (5.3)	7/16" (10.6)	26 lbs (12 kg)	270	5	30	5.1 × 32


()units in mm

LARGE UTILITY HOOK


NSF COMPONENT | RoHS | STAINLESS 303 STEEL | LOAD CAPACITY 12~22 kg 26~48 lbs | TEST 4 P.696 | STAINLESS


JF-50, 80, 120






Installation







Material	Finish
303 Stainless Steel	Mirror


Item No.	D	W	W1	H	H1	H2	H3	C	C1	t	t1	d1	d2	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Screw
JF-50	2" (50)	1/2" (12)	3/8" (10)	2-15/16" (74)	1-5/16" (34)	1-13/16" (46)	1-1/8" (28)	13/16" (20)	5/16" (8.5)	1/8" (3.5)	3/16" (5)	1/8" (3.8)	1/4" (7.2)	26 lbs (12 kg)	40	20	120	3.5 × 16
JF-80	3-1/8" (80)	5/8" (16)	1/2" (13)	4-1/2" (115)	2" (50)	2-9/16" (65)	2" (50)	1-3/16" (30)	9/16" (15.0)	3/16" (4.0)	1/4" (6)	3/16" (4.3)	5/16" (8.6)	44 lbs (20 kg)	95	6	36	4.1 × 20
JF-120	4-3/4" (120)	11/16" (18)	9/16" (14)	7-7/8" (200)	3-9/16" (90)	4-7/16" (112)	3-7/16" (88)	2-3/4" (70)	11/16" (17.0)	1/4" (5.5)	5/16" (8)	3/16" (5.3)	7/16" (10.6)	48 lbs (22kg)	260	5	30	5.1 × 32

()units in mm

LARGE UTILITY HOOK — JFT-180, 260

NSF COMPONENT · RoHS compliant · STAINLESS 303 STEEL · LOAD CAPACITY 10~15 kg 22~33 lbs · STAINLESS





JFT-180 JFT-260


Material	Finish
303 Stainless Steel	Mirror

Item No.	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)	Screw
JFT-180	22 lbs (10)	180	5	30	4.5 × 25
JFT-260	33 lbs (15)	380			5.1 × 38

LARGE UTILITY HOOK — XL-CUJ

RoHS compliant · STAINLESS 303 STEEL · LOAD CAPACITY 14~19 kg 30~42 lbs · STAINLESS





Material	Finish
303 Stainless Steel	Mirror Satin combination


Item No.	D	W	W1	(H)	(H1)	P1	P2	t	t1	d1	d2	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Screw
XL-CUJ-45TT	1-13/16" (46)	1/2" (12)	3/8" (10)	2-15/16" (75)	1-7/16 (36)	5/16" (8.5)	13/16" (20)	3/16 (4.5)	1/4" (6)	1/8" (3.8)	1/4" (7.2)	42 lbs (19 kg)	48	20	120	3.5 × 20
XL-CUJ-70TT	2-13/16" (72)			4-7/16" (112)	2-3/16" (56)	3/8" (10.0)	1-3/8" (35)			3/16" (4.3)	5/16" (8.6)	30 lbs (14 kg)	82	10	60	4.0 × 20

()units in mm

LARGE UTILITY HOOK — XL-CUF

RoHS compliant · STAINLESS 303 STEEL · LOAD CAPACITY 15~32 kg 33~72 lbs · STAINLESS





Material	Finish
303 Stainless Steel	Mirror Satin Combination

Item No.	D	(H)	(H1)	P1	P2	P3	t	t1	d1	d2	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Screw
XL-CUF-110TT	4-3/4" (120)	7-13/16" (198)	3-9/16" (91.0)	11/16" (17)	-	2-3/4" (70)	5/16" (7.5)	3/8" (10)	3/16" (5.2)	7/16" (10.5)	70 lbs (32 kg)	357	5	30	5 × 30
XL-CUF-170TT	6-13/16" (173)	11-13/16" (300)	5-7/16" (138.5)	13/16" (20)	2-3/16" (55)	4-5/16" (110)	5/16" (7.5)	3/8" (10)	1/4" (6.2)	1/2" (12.5)	33 lbs (15 kg)	552		20	6 × 30

()units in mm

LARGE HOOK


RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 20 kg 44 lbs | LOAD CAPACITY 38 kg 83 lbs | 5×30 STAINLESS

XL-SB210

- Stainless steel hook with dimensional design.
- Two-in-one hook.



Mirror Satin



Item No.	Load Capacity (kg)		Weight (g)	Box (pcs)	Carton (pcs)
	Upper	Lower			
XL-SB210/M	44 lbs (20)	83 lbs (38)	500	2	20
XL-SB210/S					

()units in mm

Material	Finish
304 Stainless Steel	Mirror (M), Satin (S)

LARGE HOOK


RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 38 kg 83 lbs | 5×30 STAINLESS

XL-SF115

- Stainless steel hook with dimensional design.



Mirror Satin



Item No.	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
XL-SF115/M	83 lbs (38)	280	4	40
XL-SF115/S				


Material	Finish
304 Stainless Steel	Mirror (M), Satin (S)

HOOK

RoHS compliant | STAINLESS 303 STEEL | LOAD CAPACITY 10 kg 22 lbs | 4×20 STAINLESS

DS-H-50, 60





Material	Finish
303 Stainless Steel	Mirror

Item No.	D	C	H	H1	L	M	t	Load Capacity	Weight (g)	Box (pcs)
DS-H-50	2" (50)	1-3/8" (35)	2-3/4" (70)	1-3/16" (30)	2-3/16" (55)	13/16" (20)	1/4" (6)	22 lbs (10 kg)	100	5
DS-H-60	2-3/8" (60)		3-15/16" (100)	1-9/16" (40)					105	


()units in mm

HOOK

RoHS compliant | STAINLESS 303 STEEL | LOAD CAPACITY 20 kg 44 lbs | 4×20 STAINLESS

KB-H-35, 40





Material	Finish
303 Stainless Steel	Mirror

Item No.	D	C	H	H1	L	M	t	Load Capacity	Weight (g)	Box (pcs)
KB-H-35	1-3/8" (35)	1-1/16" (27)	1-3/4" (45)	7/8" (22)	1-9/16" (40)	1/2" (13)	3/16" (4)	44 lbs (20 kg)	50	10
KB-H-40	1-9/16" (40)		2" (50)	1" (25)					55	

()units in mm


HOOK

NSF COMPONENT | RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 16 kg 35 lbs | TEST 4 P.696 | 3.1×16 STAINLESS

TA-3



- Anti-rotation pin prevents hook from turning.



Material	Finish
304 Stainless Steel	Mirror

Item No.	D	W	H	H1	t	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
TA-3S	7/8" (22)	3/8" (9)	1-1/8" (29)	5/8" (16)	3/16" (4.0)	35 lbs (16 kg)	10	30	600
TA-3L	1-3/16" (30)	3/8" (10)	1-5/16" (34)	7/8" (22)	1/4" (5.5)		19	20	400

()units in mm


HOOK

NSF COMPONENT | RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 8~10 kg 17.6~22 lbs | 4.1×16 STAINLESS

XL-HJT



Mirror | Mirror and Satin combination



- 304 stainless steel hooks.
- Available in Mirror (M) or Combination of Mirror and Satin (TT) finish.

Material	Finish	
	M	TT
304 Stainless Steel	Mirror	Mirror and Satin Combination

Item No.	D	W	H	H1	P1	P2	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
XL-HJT-55/M	1-5/16" (33)	9/16" (15)	2-3/16" (55)	15/16" (23)	5/16" 8)	3/4" (19)	22.0 lbs (10 kg)	34	30	300
XL-HJT-55/TT										
XL-HJT-70/M	1-11/16" (43)	11/16" (18)	2-3/4" (70)	1-3/16" (30)	3/8" (10)	15/16" (23)	17.6 lbs (8 kg)	53	20	200
XL-HJT-70/TT										


()units in mm

HOOK

RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 8~10 kg 17.6~22 lbs | TEST 4 P.696 | 4.1×16 STAINLESS

HJT





- 3/16" (4 mm) thick material designed for excellent durability.

Material	Finish
304 Stainless Steel	Satin (S)/Black (BL)

Item No.	D	H	H1	t	W	C1	C2	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
HJT-55S	1-5/16" (33)	2-3/16" (55)	15/16" (23)	3/16" (4)	9/16" (15)	5/16" (8)	3/4" (19)	22.0 lbs (10)	34	30	300
HJT-55SBL											
HJT-70S	1-11/16" (43)	2-3/4" (70)	1-3/16" (30		11/16" (18)	3/8" (10)	15/16" (23)	17.6 lbs (8)	53	20	200
HJT-70SBL											


()units in mm

FORK HOOK

NSF COMPONENT | RoHS compliant | LOAD CAPACITY 20~30 kg 44~66 lbs | 4.1×20 3.5x20 STAINLESS

EU





- Hook with unique design.
- Can hang 3 items at the same time: two on the tips and one on the neck.
- Two-tip shape ideal to hang hats, caps etc.

Item No.	W1	(W2)	D1	D2	(D3)	D4	H1	H2	d	d1	P1	P2
EU-50	7/8" (22)	1-1/2" (38)	1-1/2" (38)	3/16" (4)	11/16" (17.8)	3/16" (5)	2" (50)	3/8" (9)	3/16" (4)	5/16" (7.4)	1/4" (7)	13/16" (20)
EU-72	1-1/4" (32)	2-3/16" (56)	2-1/16" (52)	1/4" (6)	15/16" (23.0)	5/16" (8)	2-13/16" (72)	9/16" (14)	3/16" (4.6)	5/16" (8.6)	3/8" (10)	1-5/16" (34)

()units in mm

Item No.	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
EU-50	44 lbs (20)	42	20	120
EU-72	66 lbs (30)	118	10	60


Material	Finish
316 Stainless Steel	Mirror

HOOK

NSF COMPONENT | RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 20 kg 44 lbs | STAINLESS

EL-25, 30





Material	Finish
304 Stainless Steel	Mirror

Item No.	D	H	H1	t	t1	W	C1	C2	d1	d2	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Screw
EL-25	1" (26)	1-9/16" (40)	3/4" (19)	1/4" (5.5)	3/16" (4)	1/2" (12)	3/16" (5)	1/2" (12)	1/8" (3)	1/4" (6)	44 lbs (20 kg)	19	30	300	2.7 × 16
EL-30	1-1/4" (32)	2-1/8" (54.5)	1" (25)	1/4 (6.0)	3/16" (5)	9/16" (15)	1/4" (6)	5/8" (16)	3/16" (4)	5/16" (8)		32	20	200	3.8 × 20


()units in mm

HOOK

NSF COMPONENT | RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 20 kg 44 lbs | STAINLESS

EP-25, 40





Material	Finish
304 Stainless Steel	Mirror

Item No.	D	W	H	H1	H2	t	t1	C	d1	d2	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Screw
EP-25	1" (25)	1-1/8" (28)	1" (25)	1/2" (12)	3/4" (19)	3/16" (4)	3/16" (5)	11/16" (18)	1/8" (3)	1/4" (6)	44 lbs (20 kg)	16	30	300	2.7 × 16
EP-40	1-1/4" (32)	1-7/16" (36)	1-5/16" (33)	5/8" (16)	1" (25)	3/16" (5)	1/4" (6)	15/16" (23)	3/16" (4)	5/16" (8)		31	20	200	3.8 × 20


()units in mm

HOOK

NSF COMPONENT | RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 10~12 kg 22~26 lbs | STAINLESS

FC-50, 65





Material	Finish
304 Stainless Steel	Mirror

Item No.	D	H	H1	t	C	d1	d2	E	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Screw
FC-50	1-7/8" (47)	1-7/16" (37)	1-1/8" (28)	1/8" (3)	3/4" (18.5)	1/8" (3.3)	1/4" (6.5)	1/4" (6.5)	22 lbs (10 kg)	25.0	40	480	3.1 × 16
FC-65	2-9/16" (65)	1-3/4" (44)	1-3/8" (35)	3/16" (4)	7/8" (22.5)	3/16" (4.2)	5/16" (8.0)	5/16" (8.0)	26 lbs (12 kg)	54.5	20	240	3.8 × 20


()units in mm


HOOK

RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 9.4 kg 20 lbs | TEST 4 P.696


RN-50







• Designed for use on partitions.



Installation

Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
RN-50	20 lbs (9.4 kg)	17	40	400


Material	Finish
304 Stainless Steel	Satin


DOUBLE HOOK

RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 5 kg 11 lbs | TEST 4 P.696 | 3×16 STAINLESS

RI-074







• Unique two-in-one hook.

Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
RI-074	11 lbs (95 kg)	16	40	400


Material	Finish
304 Stainless Steel	Satin

DOUBLE HOOK


RoHS compliant | STAINLESS 304 STEEL | TEST 4 P.696 | 3×16 STAINLESS

RB-102





• Can be used as a light duty tie up cleat.



Installation

Item No.	Weight (g)	Box (pcs)	Carton (pcs)
RB-102	16	40	400


Material	Finish
304 Stainless Steel	Satin

HOOK HJ


NSF COMPONENT | RoHS | STAINLESS 304 STEEL | LOAD CAPACITY 8~10 kg 17.6~22 lbs | STAINLESS



HJ-50 HJ-30SBL



• Ideal for undermount applications.



Installation

Material	Finish
304 Stainless Steel	Satin/Black (BL)


Item No.	D	C	H	H1	A	B	t	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
HJ-20	1-1/8" (28.0)	11/16" (18)	1-1/16" (27.0)	7/16" (11.0)	1/2" (13)	11/16" (17)	1/8" (2.5)	22.0 lbs (10)	11	120	1200
HJ-20SBL											
HJ-30*	1-5/16" (33.0)	13/16" (20)	1-1/4" (32.5)	1/2" (13.5)	5/8" (16)			17.6 lbs (8)	15	30	600
HJ-30SBL											
HJ-50*	1-11/16" (43.5)	1-3/16" (30)	1-7/8" (47.0)	3/4" (19.6)	13/16" (21)	7/8" (22)		22.0 lbs (10)	30	40	800
HJ-50SBL											

()units in mm ⋆ NSF Component


HOOK 2H

NSF COMPONENT | RoHS | STAINLESS 304 STEEL | LOAD CAPACITY 6~10 kg 13.2~22 lbs | STAINLESS





• Unique design, also can be used as a pull.



Installation

Material	Finish
304 Stainless Steel	Satin


Item No.	L	C	C1	H	B	d	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Screw
2H-20	1-1/8" (28.0)	11/16" (18.0)	3/8" (10)	1-3/16" (30)	11/16" (18)	3/16" (4.62)	22.0 lbs (10 kg)	13	120	1200	3.1 × 16
2H-30	1-1/4" (32.5)	13/16" (20.0)	1/2" (13)	1-9/16" (39)		3/16" (4.70)		18	100	1000	3.5 × 16
2H-40	1-3/8" (35.0)	7/8" (21.5)	5/8" (16)	1-3/4" (44)	15/16" (23)		13.2 lbs (6 kg)	23	80	800	
2H-50	1-11/16" (43.0)	1-3/16" (30.0)	11/16" (18)	2-3/16" (56)	1" (25)			34	50	500	

()units in mm

HOOK HJU

RoHS | STAINLESS 304 STEEL | LOAD CAPACITY 8~10 kg 17.6~22 lbs | 3.5×20 STAINLESS





Material	Finish
304 Stainless Steel	Satin

Item No.	D	P	H	H1	A	B	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
HJU-30S	1-1/4" (32.5)	13/16" (20)	1" (25.0)	1/2" (13)	1/2" (13)	1-5/8" (41.8)	17.6 lbs (8 kg)	15	30	600
HJU-50S	1-11/16" (43.5)	1-3/16" (30)	1-1/2" (38.5)	11/16" (18)	11/16" (18)	2-5/16" (59.0)	22.0 lbs (10 kg)	30	40	800


()units in mm

UNDERMOUNT HOOK

4HJU-40M

• Chamfered edges prevent injury.






Item No.	Material	Finish	Load Capacity	Weight (g)
4HJU-40M	304 Stainless Steel	Mirror	33.7 lbs (15.3 kgf)	42.5

UNDERMOUNT HOOK

5HJU-60M

• Chamfered edges prevent injury.







Item No.	Material	Finish	Load Capacity	Weight (g)
5HJU-60M	304 Stainless Steel	Mirror	44.9 lbs (20.4 kgf)	130

CURTAIN TIE BACK HOOK KB-F-70









Item No.	Weight (g)	Box (pcs)	Carton (pcs)
KB-F-70	46	5	50

Part Name	Material	Finish
Mounting plate	304 Stainless Steel	Polished
Hook	303 Stainless Steel	

CURTAIN TIE BACK HOOK KB-F-75







Item No.	Weight (g)	Box (pcs)	Carton (pcs)
KB-F-75	56	5	50


Part Name	Material	Finish
Mounting plate	304 Stainless Steel	Polished
Hook	303 Stainless Steel	

WIRE HOOK

NSF COMPONENT | RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 3~8 kg 6.6~17.6 lbs | TEST 4 P.696

TY





Material	Finish
304 Stainless Steel	Polished

Item No.	D	D1	H	d	d1	d2	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
TY-20	7/8" (21.8)	7/16" (11)	9/16" (14)	1/8" (2.7)	1/4" (6.5)	3/16" (4.5)	6.6 lbs (3 kg)	1.5	200	7200
TY-25	1-1/16" (27.0)	1/2" (13)	11/16" (17)	1/8" (3.0)	1/4" (7.0)	3/16" (5.0)		3.0	100	3600
TY-30	1-1/4" (31.2)	9/16" (15)	13/16" (20)	1/8" (3.5)	5/16" (8.0)	1/4" (6.0)	15.4 lbs (7 kg)	5.0		1800
TY-35-15	1-7/16" (36.5)	9/16" (15)	15/16" (23)	3/16" (4.0)	3/8" (9.0)	1/4" (6.5)		7.0	50	
TY-40-15	1-11/16" (43.5)		1-1/16" (27)	3/16" (4.5)	3/8"(10.0)	5/16" (7.5)	17.6 lbs (8 kg)	11.0		900


()units in mm

WIRE HOOK

RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 3~12 kg 6.6~26 lbs | TEST 4 P.696

TF





Material	Finish
304 Stainless Steel	Polished

Item No.	D	D1	H	d	d1	d2	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
TF-20	13/16" (20.8)	7/16" (11)	13/16" (20)	1/8" (2.7)	1/4" (6.5)	3/16" (4.5)	6.6 lbs (3 kg)	3.0	200	7200
TF-30	1-1/8" (29.2)	9/16" (15)	1" (26)	1/8" (3.5)	5/16" (8.0)	1/4" (6.0)	15.4 lbs (7 kg)	5.5	100	1800
TF-35	1-9/16" (40.5)	13/16" (20)	1-3/8" (35)	3/16" (4.5)	3/8" (10.0)	5/16" (7.5)	26.0 lbs (12 kg)	13.5	50	900


()units in mm

WIRE HOOK

RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 5~12 kg 11~26 lbs | TEST 4 P.696

TL





Material	Finish
304 Stainless Steel	Polished

Item No.	D	D1	H	d	d1	d2	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
TL-15	11/16" (16.8)	7/16" (11)	9/16" (15)	1/8" (2.7)	1/4" (6.5)	3/16" (4.5)	11 lbs (5 kg)	1.9	200	7200
TL-20	7/8" (22.8)		13/16" (20)					2.1	100	3600
TL-30	1-1/8" (29.2)	9/16" (15)	1" (25)	1/8" (3.5)	5/16" (8.0)	1/4" (6.0)		6.0	50	900
TL-40	1-9/16" (40.5)	13/16" (20)	1-5/16" (34)	3/16" (4.5)	3/8" (10.0)	5/16" (7.5)	26 lbs (12 kg)	13.5	50	900

()units in mm

HOOK

STAINLESS 304 STEEL | LOAD CAPACITY 2 kg 4.4 lbs | 1.5×28 STAINLESS


PF





Pin/Stainless Steel ø1.5

• For Dry Wall Mount.



Material	Finish/Color
304 Stainless Steel	Mirror

Item No.	D	W	H	H_1	t	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
PF-22	7/8" (22)	3/8" (9)	1-3/16" (30)	5/8" (16)	3" (1/8)	4.4 lbs (2 kg)	13	20	200
PF-30	1-3/16" (30)	3/8" (10)	1-3/8" (35)	7/8" (22)	4" (3/16)		23		


()units in mm

HOOK

RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 5~8 kg 11~17.6 lbs | TEST 4 P.696

CH





Material	Finish/Color
304 Stainless Steel	Mirror

Item No.	D	D_1	W	H	H_1	d	C	t	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
CH-S	7/8" (22)	11/16" (17)	3/8" (9)	1-1/16" (27)	9/16" (15)	1/8" (3.1)	3/8" (9)	3/16" (4)	11.0 lbs (5 kg)	10.0	30	600
CH-L	1-3/16" (30)		3/8" (10)	1-5/16" (33)	7/8" (22)		7/16" (11)	3/16" (5)	17.6 lbs (8 kg)	18.5	20	400

()units in mm


LATCH HOOK

LOAD CAPACITY 60 kg 132 lbs | 5×30 STAINLESS | **EN-R100F**





- Keeps items hooked, ideal for vibration or shock applications.
- Swivels 180 degrees.



Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
EN-R100F	132 lbs (60 kg)	350	10	50

Material	Finish
316 Stainless Steel	Polished

LATCH HOOK (W/PADLOCK HOLE)

STAINLESS 304 STEEL | STAINLESS | **EN-R80-K**





Closed




Open

- Keeps items hooked, ideal for vibration or shock applications.
- Can be used with padlock.







Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
EN-R80-K	44 lbs (20 kg)	180	10	60


No.	Part Name	Material	Finish
①	Body	304 Stainless Steel	Mirror
②	Cover	316 Stainless Steel	
③	O ring	EPDM	Black
④	Lever	304 Stainless Steel	Mirror
⑤	Shaft	316 Stainless Steel	Plain
⑥	Shaft for cover		

LATCH HOOK EN-K

NSF COMPONENT | RoHS compliant | LOAD CAPACITY 20~60 kg 44~132 lbs | 4×25 STAINLESS







- Keeps items hooked, ideal for vibration or shock applications.

Material	Finish
316 Stainless Steel	Polished

Item No.	D	C	B	H	H_1	d	W	Load Capacity		Weight (g)	Box (pcs)	Carton (pcs)
								Hook	Arm			
EN-K 84	3-5/16" (84)	2-1/2" (64)	5/8" (16)	1-1/2" (38)	3/8" (10)	3/16", 5/16" (4.5, 8.5)	Max. 3/8" (10)	44 lbs (20)	22 lbs (10 kg)	92	10	120
EN-K120	4-3/4" (120)	3-3/4" (96)	7/8" (22)	2-1/8" (54)	1/2" (12)	3/16", 7/16" (5.4,10.5)	Max. 2-3/8" (20)	132 lbs (60)		280		60


()units in mm

LATCH HOOK EN-R80

NSF COMPONENT | RoHS compliant | LOAD CAPACITY 20 kg 44 lbs | 4×25 STAINLESS







- Keeps items hooked, ideal for vibration or shock applications.


Item No.	Load Capacity		Weight (g)	Box (pcs)	Carton (pcs)
	Hook	Arm			
EN-R80	44 lbs (20 kg)	22 lbs (10 kg)	85	10	120

Material	Finish
316 Stainless Steel	Polished

LATCH HOOK WH

NSF COMPONENT | STAINLESS 304 STEEL | LOAD CAPACITY 15 kg 33 lbs | 3.5×16 STAINLESS





- Keep items hooked, ideal for vibration or shock applications.

Item No.	L	H	S	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
WH-1	1-1/2" (38)	1" (25)	1/4"(7)	33 lbs (15 kg)	40	20	200
WH-2	1-5/8" (41)	1-5/16" (34)	3/8" (10)		55		

()units in mm

Material	Finish
304 Stainless Steel	Plain

SWING HOOK (W/FRICTION)


NSF COMPONENT | RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 10 kg 22 lbs | TEST 4 P.696 | 4×20 STAINLESS


JF-T


- Swivels 180 degrees.
- Hook has constant torque when swiveling.
- Ideal for vibration or shock applications.




JF-T45 JF-T70 JF-T100









Item No.	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
JF-T45	37 lbs (17 kg)	90	10	100
JF-T70		225		
JF-T100	88 lbs (40 kg)	638	5	20

Material	Finish
304 Stainless Steel	Mirror


LARGE SWING LATCH HOOK (W/FRICTION)

RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 40 kg 88 lbs | 4×20 STAINLESS

JN-T100

- Swivels 180 degrees.
- Hook has constant torque when swinging.
- Ideal for vibration or shock applications.





Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
JN-T100	88 lbs (40 kg)	780	5	20

No.	Part Name	Material	Finish
①	Strike	304 Stainless Steel	Mirror
②	Hook	303 Stainless Steel	
③	Arm	304 Stainless Steel	
④	Shaft	303 Stainless Steel	Plain
⑤	Back Plate	304 Stainless Steel	


STAINLESS STEEL FRICTION TYPE LARGE HOOK — HK-TS




HK-TS100




HK-TS70



- Hook swivels 180°.
- Friction prevents unintended swivelling caused by vibrations.
- Ball shaped tip prevents injury.
- Double-hook type (HK-TT) is also available.



HK-TS70



HK-TS100

Item No.	Load Capacity	Weight (g)
HK-TS70	22.5 lbs (10.2 kg)	230
HK-TS100	58.4 lbs (26.5 kg)	550

No.	Part Name	Material	Finish
①	Hook	304 Stainless Steel	Polished
②	Mount	Stainless Steel	


STAINLESS STEEL FRICTION TYPE DOUBLE LARGE HOOK — HK-TT




HK-TT100




HK-TT70



- Hook swivels 180°.
- Friction prevents unintended swivelling caused by vibrations.
- Ball shaped tip prevents injury.
- Single-hook type (HK-TS) is also available.



HK-TT70



HK-TT100

Item No.	Load Capacity	Weight (g)
HK-TT70	22.5 lbs (10.2 kg)	260
HK-TT100	58.4 lbs (26.5 kg)	600

No.	Part Name	Material	Finish
①	Hook	304 Stainless Steel	Polished
②	Mount	Stainless Steel	


* Load capacity values are for one side only.

SWING HOOK


RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 8~12 kg 17~26 lbs | TEST 4 P.696 | STAINLESS

TK, TKF





- Swivels 180 degrees.
- Type “F” models have constant torque when swiveling.
- Ideal for vibration or shock applications.



Installation

Material	Finish
304 Stainless Steel	Polished

Item No.	Type	A	B	C	R	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
TK-30	Without Friction	9/16" (14.5)	15/16" (23.4)	1-7/16" (36.0)	3/8" (10)	26 lbs (12 kg)	17	100	1000
TK-45	Without Friction	3/4" (19.4)	1-1/8" (28.4)	1-3/4" (44.3)	9/16" (15)	17 lbs (8 kg)	20		
TK-30F	With Friction	9/16" (14.5)	15/16" (23.4)	1-7/16" (36.0)	3/8" (10)	26 lbs (12 kg)	17	100	1000
TK-45F	With Friction	3/4" (19.4)	1-1/8" (28.4)	1-3/4" (44.3)	9/16" (15)	17 lbs (8 kg)	20		

()units in mm


BUTTERFLY HOOK


RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 3~6 kg 6.6~13.2 lbs | TEST 4 P.696 | 4×12 STAINLESS

TZ-360











- Hinged flap allows flush or corner mount.
- Applicable angle: 90°~270°


A. 180° Surface, Flush



B. 270° Surface, Inner Corner



C. 90° Outer Corner



Installation

Material	Finish
304 Stainless Steel	Polished

Item No.	Load Capacity A	Load Capacity B	Load Capacity C	Weight (g)	Box (pcs)	Carton (pcs)
TZ-360	13.2 lbs (6 kg)	12.3 lbs (5.6 kg)	6.6 lbs (3 kg)	27	50	500

BUTTERFLY HOOK


RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 3~8 kg 6.6~17.6 lbs | 4×12 STEEL

DZ-270











- Eyelet swivels for various installation applications.
- Hinged leaves for flush or corner mount.
- Includes ½" (M4 × 12) long screws.


Installation



A. 270° Surface, Inner Corner



B. 180° Surface, Flush



C. 90° Outer Corner

Material	Finish
304 Stainless Steel	Polished

Item No.	Load Capacity A (270°)		Load Capacity B (180°)		Load Capacity C (90°)		Weight (g)	Box (pcs)	Carton (pcs)
DZ-270	Horizontal	Vertical	Horizontal	Vertical	Horizontal	Vertical	29	50	500
	12.3 lbs (5.6 kg)	13.2 lbs (6 kg)	13.2 lbs (6 kg)	17.6 lbs (8 kg)	6.6 lbs (3 kg)	17.6 lbs (8 kg)			

EYE HOOK

RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 5.3~10.6 kg 11.7~23.4 lbs | TEST 4 P.696 | 3.5×16 STEEL


RF-D35



Ⓐ Horizontal



Ⓑ Vertical



- Eyelet swivels for various installation applications.
- Can be mounted horizontally to walls or under-mounted for vertical applications.
- Includes 5/8" (M3.5 × 16) long screws.


Item No.	Load Capacity		Weight (g)	Box (pcs)	Carton (pcs)	Material	Finish
RF-D35	Ⓐ 11.7 lbs (5.3 kg)	Ⓑ 23.4 lbs (10.6 kg)	27	50	400	304 Stainless Steel	Satin

ROTATING/SWING HOOK

RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 6.1 kg 13 lbs | TEST 4 P.696 | 3×25 STAINLESS

RF-U50





- Rotates 360º and swings 180º.
- Can be mounted in various directions.


Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Material	Finish
RF-U50	13 lbs (6.1 kg)	40	25	250	304 Stainless Steel	Satin

ROTATING HOOK

NSF COMPONENT | RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 3 kg 6.6 lbs | TEST 4 P.696 | 3×25 STAINLESS

RF-50





- Rotates 360º.
- Can be mounted in various directions.


Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Material	Finish
RF-50	6.6 lbs (3 kg)	33	25	500	304 Stainless Steel	Satin

SWING HOOK

STAINLESS 304 STEEL | STAINLESS 303 STEEL | LOAD CAPACITY 50 kg 110 lbs | TEST 4 P.696 | 4×20 STAINLESS

XL-JSF40TT





- Vertical swivel allows for under mount applications.

Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
XL-JSF40TT	110 lbs (50 kg)	70	20	120


Part Name	Material	Finish
Hook	303 Stainless Steel	Mirror/Satin Combination
Bracket	304 Stainless Steel	

SWING HOOK

RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 5.6~6.7 kg 12~14 lbs | TEST 4 P.696 | 4×16 STAINLESS

UC





- Vertical swivel allows for under mount applications.

Material	Finish
304 Stainless Steel	Satin

Item No.	W	D	H	H_1	H_2	H_3	C	R	t	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
UC-048	3/8" (9)	1" (24.9)	2-3/16" (55)	1-7/8" (48)	13/16" (21.4)	2-9/16" (64.5)	1/4" (6.5)	3/8" (10.0)	1/16" (2.0)	12 lbs (5.6 kg)	37	40	400
UC-055	3/8" (10)	1-3/16" (30.8)	2-7/16" (62)	2-3/16" (55)	1" (25.5)	2-13/16" (71.5)	3/16" (5.0)	1/2" (12.5)	1/8" (2.5)	14 lbs (6.7 kg)	45	25	250


()units in mm

SWING HOOK

NSF COMPONENT | RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 6.7~8.9 kg 14~19 lbs | TEST 4 P.696 | 4×16 STAINLESS

UJ





- Rotates 360° and swivels 180°.
- Can be mounted in various directions.

Material	Finish
304 Stainless Steel	Satin


Item No.	W	W_1	D	D_1	D_2	H	H_1	H_2	P	E	R	t	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
UJ-040	5/8" (16)	3/8" (9)	5/8" (16.5)	1/4" (5.5)	1" (24.9)	1-5/8" (42)	1-9/16" (40)	13/16" (21.4)	1-3/16" (30)	ø3/8" (9)	3/8" (10.0)	2.0" (2.0)	14 lbs (6.7 kg)	27	50	500
UJ-050	11/16" (18)	3/8" (10)	3/4" (19.0)	1/4" (7.0)	1-3/16" (30.8)	1-7/8" (48)	2" (50)	1" (25.5)	1-3/8" (35)	ø3/8" (10)	1/2" (12.5)	1/8" (2.5)	19 lbs (8.9)	45	30	300

()units in mm

SLIDE HOOK

4x20 STAINLESS | STAINLESS 303 STEEL | STAINLESS 304 STEEL


HK-CS30



- An extendable and retractable hook designed to be easily surface-mounted underneath tables, desks, and shelves.
- Low profile, space-saving design.
- Specially designed guide ensures smooth operation.

Application





No.	Part Name	Material	Finish
①	Arm	304 Stainless Steel	Barrel Polished
②	Base		
③	Shaft	303 Stainless Steel	-
④	Wave Washer	Stainless Steel	
⑤	Plastic Washer	Polyacetal (POM)	

Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
HK-CS30	22.4 lbs (10.2 kg)	190	10	40

LONG PROJECTION HOOK


RoHS compliant | STAINLESS 304 STEEL | STAINLESS 303 STEEL | LOAD CAPACITY 20.2 - 47.1 lbs (9.2 - 21.4 kg) | 4x20 STAINLESS


KB-H-L




- Choose the perfect length for your storage needs.
- A creative storage solution for bulky items.
- Take advantage of deep, recessed spaces.

Application Example


Paper Bag Holder


Cable Management



No.	Part Name	Material	Finish
①	Arm	303 Stainless Steel	Mirror
②	Base	304 Stainless Steel	

Item No.	D	D_1	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
KB-H-55L-SM	2-5/32" (55 mm)	1-9/16" (40 mm)	47.1 lbs (21.4 kg)	56	10	200
KB-H-85L-SM	3-11/32" (85 mm)	2-3/4" (70 mm)	26.8 lbs (12.2 kg)	67		100
KB-H-110L-SM	4-11/32" (110 mm)	3-3/4" (95 mm)	20.2 lbs (9.2 kg)	73		100


()units in mm

HANGER PLATE


RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 10 kg 22 lbs | TEST 3 P.696 | STAINLESS

AP





AP-20



AP-25, 32

Material	Finish
304 Stainless Steel	Polished


Item No.	B1	B2	B3	H	A	C1	C2	C3	d	E1	E2	E3	T	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Screw
AP-20	13/16" (20)	3/8" (9.2)	3/8" (9.2)	1-3/16" (30.4)	7/16" (11.8)	1/2" (12)	3/16" (5.0)	-	1/8" (2.8)	1/16" (2.0)	11/16" (16.8)	9/16" (13.6)	1/4" (6)	22 lbs (10 kg)	6	100	1000	2.7 × 13
AP-25	1" (25)	7/16" (11.5)	7/16" (11.5)	1-1/2" (37.5)	9/16" (14.7)	9/16" (14)	1/4" (6.5)	3/8" (9)	1/8" (3.3)	1/8" (2.5)	13/16" (20.5)	11/16" (17.0)	5/16" (8)		10			3.1 × 16
AP-32	1-1/4" (32)	9/16" (14.8)	9/16" (14.8)	1-7/8" (47.0)	11/16" (17.2)	11/16" (18)	5/16" (8.0)	1/2" (12)	3/16" (4.2)	1/8" (3.2)	15/16" (24.5)	7/8" (22.5)	3/8" (10)		16			3.5 × 16


()units in mm

HANGER PLATE


RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 10 kg 22 lbs | TEST 3 P.696 | STAINLESS

SP







SP-17, 22



SP-30





Material	Finish
304 Stainless Steel	Polished

Item No.	B	B1	H	A	C1	C2	C3	C4	d	E1	E2	T	t	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)	Screw
SP-17	11/16" (17)	7/16" (10.5)	1-1/8" (28.5)	1/4" (7)	5/16" (8)	3/16" (4.5)	9.5" (9.5)	-	1/8" (2.7)	1/8" (3.5)	3/16" (4)	3/16" (4)	1/16" (1.2)	22 lbs (10 kg)	4	200	1000	2.7 × 13
SP-22	7/8" (22)	9/16" (14.0)	1-7/16" (36.5)	3/8" (10)	1/2" (13)	1/4" (6.0)	3/8" (10.0)	-	1/8" (3.3)	3/16" (4.5)	1/4" (6)	3/16" (5)	1/16" (1.5)		8			3.1 × 16
SP-30	1-3/16" (30)	11/16" (18.0)	1-11/16" (43.5)	1/2" (12)	13/16" (20)	3/8" (9.5)	3/8" (10.0)	1/4" (5.5)	3/16" (4.2)	3/16" (5.0)	1/4" (7)	1/4" (6)			13	100	500	3.5 × 16

()units in mm


RECESSED HOOK


RoHS compliant | LOAD CAPACITY 20 kg 44 lbs | TEST 17 P.698 | NO SCREW

NF-60




- Hook is spring loaded to retract.
- Ideal for vibration or shock applications.
- Panel Thickness: - Wood: Min. 13/16" (20 mm)
  - Sheet metal: 1/32"~1/16" (0.8~1.6 mm) with optional bracket NF-50, sold separately.





Bore Dimensions
For thickness over 1-3/16" (30 mm)



Bore Dimensions
For thickness 13/16"~1-1/8
(20~29 mm)

Part Name	Material	Finish
Body	Aluminum	Grey
Pin/Spring	304 Stainless Steel	Plain
Rubber	Polychloroprene	Black

Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
NF-60	44 lbs (20 kg)	31	10	200

SOFT CLOSE RECESSED HOOK


RoHS compliant | LOAD CAPACITY 30 kg 66 lbs | TEST 17 P.698 | NO SCREW


NF-60D




Grey Silver Metallic Silver

- Hook is spring loaded to retract with a soft closing action.
- Ideal for vibration or shock applications.
- Panel Thickness: - Wood: Min. 1" (25 mm)
  - Sheet metal: 1/32"~1/16" (0.8~1.6 mm) with optional bracket NF-50, sold separately.





Bore Dimensions
(For thickness over 1-3/16" (30 mm)




Bore Dimensions
(For thickness 1"~1-1/8" (25~29 mm)

Part Name	Material	Finish
Body	Aluminum	Grey/Silver Metallic Silver
Pin/Spring	304 Stainless Steel	Plain
Rubber	Polychloroprene	Black
Rear Cover	POM	Grey


Item No.	Finish	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
NF-60D/GR	Grey	66 lbs (30 kg)	49	10	200
NF-60D/SL	Silver				
NF-60D/MSL	Metallic Silver				

Bracket for sheet metal application







Supplied with M4×14 Stainless steel screw.



Cut Out Dimensions for NF-60



Cut Out Dimensions for NF-60D



Item No.	Weight (g)	Box (pcs)	Carton (pcs)	Material	Finish
NF-50	22	20	400	Steel	Yellow Zinc Chromate

RECESSED HOOK (W/SOFT CLOSE)


RoHS compliant | LOAD CAPACITY 9.1 kg 20 lbs | NO SCREW


NF-45D




NF-45D-GR NF-45D-BL NF-45D-SSL NF-45D-WT

- A modern, clean hook solution with Motion Design Technology.
- Hook is spring loaded to retract and soft close.
- Ideal for vibration or shock applications.
- Panel Thickness: - Wood: Min. 1-1/16~1-1/4" (27~31 mm)
  - Sheet metal: 1/32~3/16 (0.8~4.0 mm)
- Hook bracket (NF-45DB) for sheet metal sold separately.







Wood panel (27~31mm)



Wood panel (32mm or thicker)



Sheet metal



Cut Out Dimensions

No.	Part Name	Material	Finish
①	Body	Aluminum Alloy	Grey/Black/Silver White
②	Arm		
③	Cover	Polyacetal	
④	Pin	304 Stainless Steel	Plain
-	Spring		
⑤	Bumper	Rubber	Black/White

Item No.	Color	Load Capacity of Arm	Load Capacity of Base	Weight (g)	Box (pcs)	Carton (pcs)
NF-45D-GR	Grey	21 lbs·f (9.5 kg·f)	112 lbs·f (51kg·f)	32	10	200
NF-45D-BL	Black					
NF-45D-SSL	Silver					
NF-45D-WT	White					


RECESSED HOOK BRACKET


STEEL

NF-45DB



NF-45DB





- Allows for the NF-45D hook to be mounted onto sheet metal.
- Can be mounted from both front and back sides.
- Has flanges for double-sided tape, which allows for temporary fixing before mounting.

Item No.	Material	Finish	Box (pcs)	Carton (pcs)
NF-45DB	Steel	Yellow Zinc Chromate	40	40

RECESSED SNAP-IN HOOK (W/SOFT CLOSE) NF-60DF

LOAD CAPACITY 30 kg 66 lbs

- Easy Installation and removal. Surface mount (snap-in) type for sheet metal, bracket not needed.
- Hook is spring loaded to retract and soft close.
- Convenient screw installation from the front side of the hook, screw cover is provided.
- Ideal for vibration or shock applications.
- Panel thickness range for sheet metal: 1/16"~3/16" (1~4mm).




NF-60DF-BL




NF-60DF-MSL


Sheet Metal: 1/16~3/16" (1~4mm)




Cut Out Dimensions



Installation





When opened

No.	Part Name	Material	Finish
①	Body	Aluminum Alloy	Black (BL), Metallic Silver (MSL)
②	Arm		
③	Cover	Plastic (POM)	Dark Grey
④	Cushion Rubber	CR	Black, Metallic Silver
⑤	Nut	Zinc Die Cast (ZDC)	Chromate
⑥	Holding Pin		
⑦	Screw	304 Stainless Steel	Plain


Item No.	Color	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
NF-60DF-BL	Matte Black	66 lbs (30 kg)	54	10	200
NF-60DF-MSL	Metalic Silver				


COUNTER HOOKS HK-CH35




- Recessed mounted hook provides a clean appearance.
- Hook can be seen at the edge when unused.
- Hook closes and retracts with a soft-close motion into body when hooked items are removed.
- Board thickness: Min. 1" (26 mm).


Board Thickness	Qty of Spacers	Bore Depth
Min 1" (26mm)	None	11/16" (17mm)
15/16" ~1" (23~26mm)	1 pcs	9/16" (14mm)
13/16"~15/16" (20~23mm)	2 pcs	7/16" (11mm)
11/16"~13/16" (17~20mm)	3 pcs	5/16" (8 mm)








[Spacer]



[Bore Dimensions]



Item No.	Finish	LoadCapacity	Box (pcs)	Carton (pcs)
HK-CH35-BL	Black	22 lbf (10 kgf)	20	200
HK-CH35-BR	Brown			
HK-CH35-SL	Silver			

No.	Part Name	Material	Finish
①	Body	Aluminum Alloy (ADC)	Enamel Finish Black/Brown/Silver
②	Arm	AluminumAlloy (ADC)	Enamel Finish Black/Brown/Silver
③	Cover	Plastic (POM)	-
④	Bumper	PUR	Clear
⑤	Spacer	Plastic (PA)	Black

RECESSED HOOK

RoHS compliant | LOAD CAPACITY 20 kg 44 lbs | TEST 17 P.698 | NO SCREW

NF-K


Pearl Chrome


Chrome


Matte Black







- The arm section is spring loaded to automatically retract when not in use.
- The product does not protrude when the arm is folded in, creating a flush design and ensuring safety.
- Can also be mounted to sheet metal using the NF-50D or NF-50 bracket (sold separately).
- Round type (NF-R) also available.

Recommended Screw:
- 4x15 cross-recessed pan head or tapping screws. For panel thickness 1"~1-1/8" (25-29 mm)
- 4x20 cross-recessed pan head or tapping screws. For panel thicker than 1-3/16" (30 mm)


NF-K52




Wood Mounting (thickness 1"~1-1/8" (25-29 mm)




Wood Mounting (thickness 1-3/16" (30 mm) or more)




Sheet Metal Mounting




NF-K64




Wood Mounting (thickness 1"~1-1/8" (25-29 mm)




Wood Mounting (thickness 1-3/16" (30 mm) or more)




Sheet Metal Mounting




NF-K77




Wood Mounting (thickness 1"~1-1/8" (25-29 mm)



Wood Mounting (thickness 1-3/16" (30 mm) or more)



Sheet Metal Mounting



Item No.	Finish	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
NF-K52-SCR	Pearl Chrome Plating	44 lbs (20 kg)	77	10	120
NF-K52-CR	Chrome Plating				
NF-K52-BL	Matte Black				
NF-K64-SCR	Pearl Chrome Plating		95		
NF-K64-CR	Chrome Plating				
NF-K64-BL	Matte Black				
NF-K77-SCR	Pearl Chrome Plating		145		
NF-K77-CR	Chrome Plating				
NF-K77-BL	Matte Black				

No.	Part Name	Material
①	Body	Zinc Alloy
②	Arm	
③	Spring	304 Stainless Steel
④	Knurled Pin	303 Stainless Steel
⑤	Cushioning Rubber	Chloroprene Rubber

RECESSED HOOK

RoHS compliant | LOAD CAPACITY 20 kg 44 lbs | TEST 17 P.698 | NO SCREW

NF-R



Dull Chrome



Chrome



Matte Black







- Hook is spring loaded to retract.
- Ideal for vibration or shock application.




No.	Part Name	Material
①	Main Body	Zinc Alloy (ZDC)
②	Arm	
③	Spring	304 Stainless Steel
④	Knurled Pin	303 Stainless Steel
⑤	Cushioning Rubber	Chloroprene Rubber (CR)


NF-R52







NF-R64





NF-R77





Item No.	Load Capacity	Weight (g)	Finish	Box (pcs)	Carton (pcs)	Material
NF-R52-SCR	44 lbs (20 kg)	70	Dull Chrome	10	120	Zinc Alloy
NF-R52-CR			Chrome Plating	10	120	
NF-R52-BL			Matte Black	10	120	
NF-R64-SCR		90	Dull Chrome	10	120	
NF-R64-CR			Chrome Plating	10	120	
NF-R64-BL			Matte Black	10	120	
NF-R77-SCR		130	Dull Chrome	10	120	
NF-R77-CR			Chrome Plating	10	120	
NF-R77-BL			Matte Black	10	120	

VANITY HOOK

LOAD CAPACITY 5.8 kg 12.8 lbs | 3.5×30 STEEL | SSF




SSF-10/GA




SSF-10/CR-SW


- Slim 3/8" (10 mm) diameter hook with groove, useful for hanging bags, brushes, etc.
- Includes 1/8" ~ 1-3/16" (3.5 × 30 mm) long self-tapping screw.
- Available in gold (GA) or chrome (CR) with option of designer crystals, adding a touch of glamour.




SSF-10/CR
SSF-10/GA



SSF-10/CR-SW
SSF-10/GA-SW



Application



Installation

Item No.	Material	Finish	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
SSF-10/CR	Brass	Chrome	12.8 lbs (5.8 kg)	24	10	100
SSF-10/GA		Gold				
SSF-10/CR-SW	Brass, Crystal	Chrome		25		
SSF-10/GA-SW		Gold				

MAGNETIC HOOK


LOAD CAPACITY 2 kg 4.4 lbs | MJ-45








- Hook with strong magnet.
- Convenient for use on steel cabinets, refrigerators, tool cabinets etc.





Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
MJ-45/BRN	4.4 lbs (2 kg)	58	20	240
MJ-45/IVY				
MJ-45/ORG				

Material	Color
Magnet ABS	Brown (BRN) Ivory (IVY) Orange (ORG)


COAT HOOK


STAINLESS 304 STEEL | STAINLESS 303 STEEL | LOAD CAPACITY 10 kg 22 lbs | STEEL

DSH-01



• Supplied with screw, and plastic expansion anchor.





Installation

Item No.	Finish	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
DSH-01	Satin	22 lbs (10 kg)	71	25	250
DSH-01-BL	Black				

Material	Finish
303/304 Stainless Steel	Satin, Black (BL)


COAT HOOK


STAINLESS 304 STEEL | STAINLESS 303 STEEL | LOAD CAPACITY 10 kg 22 lbs | STEEL

DSH-04



• Supplied with screw, and plastic expansion anchor.





Installation

Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
DSH-04	22 lbs (10 kg)	55	25	250

Material	Finish
303/304 Stainless Steel	Satin


COAT HOOK


STAINLESS 304 STEEL | STAINLESS 303 STEEL | LOAD CAPACITY 10 kg 22 lbs | STEEL

DSH-05



• Supplied with screws and plastic expansion anchors.





Installation

Item No.	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
DSH-05	22 lbs (9 kg)	280	1	10

Material	Finish
303/304 Stainless Steel	Satin


COAT HOOK


STAINLESS 304 STEEL | STAINLESS 303 STEEL | LOAD CAPACITY 10 kg 22 lbs | STEEL

DSH-02

- Supplied with screws, brackets, plastic expansion anchors and allen key.







Installation

Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
DSH-02	22 lbs (10 kg)	178	10	100

Material	Finish
303/304 Stainless Steel	Satin


COAT HOOK


STAINLESS 304 STEEL | STAINLESS 303 STEEL | LOAD CAPACITY 10 kg 22 lbs | STEEL

DSH-03

- Supplied with screws, brackets, plastic expansion anchors and allen key.







Installation

Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
DSH-03	22 lbs (10 kg)	71	5	50

Material	Finish
303/304 Stainless Steel	Satin


COAT HOOK


STAINLESS 304 STEEL | STAINLESS 303 STEEL | LOAD CAPACITY 10 kg 22 lbs | STEEL

DSH-129

• Supplied with screw, and plastic expansion anchor.







Installation

Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
DSH-129	22 lbs (10 kg)	100	25	250

Material	Finish
303/304 Stainless Steel	Satin


COAT HOOK


STAINLESS 304 STEEL | STAINLESS 303 STEEL | LOAD CAPACITY 10 kg 22 lbs

DSH-P5

• Supplied with screw, and plastic expansion anchor.







Installation

Item No.	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
DSH-P5-20	22 lbs (10 kg)	45	25	250
DSH-P5-25		113		


Material	Finish
303/304 Stainless Steel	Satin

HOOK

NSF COMPONENT | RoHS compliant | STAINLESS 304 STEEL | LOAD CAPACITY 20 kg 44 lbs | STAINLESS

EW-65E, 80E





Material	Finish
304 Stainless Steel	Mirror

Item No.	A	C1	C	D	E	F	C2	H	H1	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)	Screw
EW-65E	2-9/16" (65)	1-7/16" (36)	1/4" (6.5)	1" (25)	3/16" (4)	3/16" (5)	5/16" (7.3)	1-5/16" (33)	13/16" (20)	44 lbs (20)	52	10	100	3.1 × 16
EW-80E	3-1/8" (80)	1-3/4" (44)	5/16" (8.0)	1-1/4" (32)	3/16" (5)	1/4" (6)	3/8" (9.0)	1-5/8" (42)	1" (25)		93			3.8 × 20

()units in mm


RUBBER HOOK (PASTEL COLOR) PXB-GR05-111




Red Yellow Green Blue White Black

- Simple and safe design.
- Base made of stainless steel provides high strength and durability.
- Available in a wide range of colors.







Item No.	Color	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
PXB-GR05-111-LRD	Red	22 lbs (10 kg)	48	10	100
PXB-GR05-111-LYE	Yellow				
PXB-GR05-111-LGN	Green				
PXB-GR05-111-LBU	Blue				
PXB-GR05-111-WT	White				
PXB-GR05-111-BL	Black				

No.	Part Name	Material	Finish
①	Base Plate	304 Stainless Steel	Plain
②	Base		
③	Cover	Silicone Rubber	-


RUBBER HOOK (HAT & COAT HOOK) PXB-GR05-211




Red Yellow Green Blue White Black

- Simple and safe design.
- Base made of stainless steel provides high strength and durability.
- Available in a wide range of colors.







Item No.	Color	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
PXB-GR05-211-RD	Red	22 lbs (10 kg)	66	10	100
PXB-GR05-211-YE	Yellow				
PXB-GR05-211-GN	Green				
PXB-GR05-211-BU	Blue				
PXB-GR05-211-WT	White				
PXB-GR05-211-BL	Black				

No.	Part Name	Material	Finish
①	Base Plate	304 Stainless Steel	Plain
②	Base		
③	Cover	Silicone Rubber	-

RUBBER HOOK (TWIN TYPE RUBBER SERIES) PXB-GR05-212

STAINLESS

LOAD CAPACITY 10.2 kg 22.4 lbs










Silicone Rubber Cover



Stainless Steel Base

- The inside of the silicone cover is equipped with an anti slip feature which significantly reduces the chance the cover will be accidentally removed.
- The base is made from stainless steel to hold items securely in place.
- No sharp or hard edges to ensure safety.
- Special orders for covers only can be made.





Bright Red



Bright Yellow



Bright Green



Bright Blue



White



Black

Item No.	Color	Load Capacity	Weight (g)
PXB-GR05-212-BRD	Bright Red	22.4 lbs (10.2 kg)	90.5
PXB-GR05-212-BYE	Bright Yellow		
PXB-GR05-212-BGN	Bright Green		
PXB-GR05-212-BBU	Bright Blue		
PXB-GR05-212-WT	White		
PXB-GR05-212-BL	Black		

*Load capacity values are for one side only.

No.	Part Name	Material	Finish
①	Base	Stainless Steel (SCS13)	Plain
②	Cover	Silicone Rubber	Bright Red Bright Yellow Bright Green Bright Blue White Black

*SCS13 is a cast steel material similar to SUS304.













RUBBER HOOK (NORDIC)


RoHS compliant | STAINLESS

PXB-GN05-101



- Simple and safe design.
- Includes pin for drywall installation.
- Available in a wide range of colors.





Item No.	Color	Load Capacitykg	Weight (g)	Box (pcs)	Carton (pcs)
PXB-GN05-101-GWT	White	9 lbs (4.1 kg)	39	10	100
PXB-GN05-101-BR	Brown				
PXB-GN05-101-BL	Black				
PXB-GN05-101-GPK	Greyish Pink				
PXB-GN05-101-GYE	Greyish Yellow				
PXB-GN05-101-GGN	Greyish Green				
PXB-GN05-101-GBU	Greyish Blue				

No.	Part Name	Material	Finish
①	Base	Zinc Alloy	Nickel
②	Cover	Silicone Rubber	-
③	Drywall Pin	AES	Plain
④	Drywall Screw	Stainless Steel	

RUBBER HOOK (MAGNETIC)


RoHS compliant

PXB-GN05M-101



- Magnetic type
- Simple and safe design.
- Available in a wide range of colors.





Item No.	Color	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
PXB-GN05M -101-GR	Grey	2.4 lbs (1.1 kg)	32	10	100
PXB-GN05M -101-GY	Green Yellow				
PXB-GN05M -101-NB	Navy Blue				
PXB-GN05M -101-GWT	White				
PXB-GN05M -101-YR	Orange				

No.	Part Name	Material	Finish
①	Base	Zinc Alloy	Plain
②	Cover	Silicone Rubber	-

RUBBER HOOK (NORDIC)


PXB-GN05-111



Dark Grey Brown Beige

- Simple and safe design.
- Base made of stainless steel provides high strength and durability.
- Designed to Integrate modern style.





Item No.	Color	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
PXB-GN05-111-DG	Dark Grey	18 lbs (8 kgf)	93	10	100
PXB-GN05-111-BR	Brown				
PXB-GN05-111-BE	Beige				

No.	Part Name	Material	Finish
①	Base	Stainless Steel	Plain
②	Cover	Silicone Rubber	-

COAT HOOK (PREMIUM WOOD SERIES)


PXB-WM05-111



White Birch Ostrya Japonica (Hornbeam) Walnut

- The contrast of the gentle touch of wood surface and shiny metallic texture creates a unique rectilinear feature.
- Metal core inside the wooden arm provides high-durability.
- Clear coating greatly improves the endurance.





No.	Part Name	Material	Finish
①	Base	Steel	Zinc Chromate
②	Base Cover	Zinc Alloy	Nickel/Black
③	Arm	Wood	Clear Coating
④	Socket Screw	Stainless Steel	Plain

Item No.	Color	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
PXB-WM05-111-MK	White Birch	22 lbs (10 kgf)	110	6	48
PXB-WM05-111-AS	Ostrya Japonica (Hornbeam)				
PXB-WM05-111-WN	Walnut				


COAT HOOK (URBAN METAL SERIES) PXB-UM05-101


Satin


Black

- An unprecedented design with sleekness from aluminum extrusion and edge treatment.
- Designed to integrate with modern style interiors where rectilinear-themed.
- Modern and minimalistic appearance add to the high quality design





Item No.	Color	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
PXB-UM05-101-ST	Satin	22 lbs (10 kg)	112	8	64
PXB-UM05-101-BL	Black				


No.	Part Name	Material	Finish
①	Base	Aluminum	Satin/Black
②	Arm		
③	Socket Screw	Stainless Steel	Plain

COAT HOOK (URBAN METAL/QUEST SERIES) PXB-UM05-101-Q1



Black


Gold

- Decorative plate fitted into hook arm represents modern luxury style.
- The combination of simple form and decorative plate suite modern/classic interior design.
- Custom engraving available by special order.







Item No.	Color	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
PXB-UM05-101-Q1-BL	Black	22 lbs (10 kgf)	114	8	64
PXB-UM05-101-Q1-GL	Gold				

No.	Part Name	Material	Finish
①	Base	Aluminum	Gold/Black
②	Arm		
③	Plate	Brass	
④	Screw	Stainless Steel	Plain

COAT HOOK

STEEL

PXB-AB05



Bronze Brown




Bronze Black




• Vintage design with brass casting.

PXB-AB05-101



PXB-AB05-111



Item No.	Color	Load Capacity	W	H	D	Weight (g)
PXB-AB05-101-BL	Bronze Black	22 lbs (10 kg)	11/16" (17 mm)	1-5/8" (42 mm)	1-9/16" (39 mm)	79
PXB-AB05-101-BR	Bronze Brown					
PXB-AB05-111-BL	Bronze Black		15/16" (23.5 mm)	2-1/4" (58 mm)	2-1/8" (54 mm)	210
PXB-AB05-111-BR	Bronze Brown					

()units in mm

No.	Part Name	Material	Finish
①	Body	Brass	Bronze Black (BL) Bronze Brown (BR)
②	Screw		
③	Sharp Pin	Stainless Steel	Plain

COAT HOOK (AGED CAST)

STEEL

PXB-AC05-111




Bronze Black



Bronze Brown



• Vintage design with brass casting.



No.	Part Name	Material	Finish
①	Body	Brass	Bronze Black (BL) Bronze Brown (BR)
②	Insert		
③	Screw	Bronze	

Item No.	Color	Load Capacity	W	H	D	Weight (g)
PXB-AC05-111-BL	Bronze Black	44 lbs (20 kgf)	1-7/16" (36)	2-1/16" (52.5)	2-1/4" (58)	400
PXB-AC05-111-BR	Bronze Brown					

()units in mm

COAT HOOK (AGED SCREW SERIES) PXB-AS05-111

STEEL




Bronze Brown



Bronze Clear

• Vintage design with brass casting.





No.	Part Name	Material	Finish
①	Body	Brass	Bronze Brown(BR) Bronze Clear(SD)
②	Insert		
③	Screw		
④			

Item No.	Color	Load Capacity	W	H	D	Weight (g)
PXB-AS05-111-BR	Bronze Brown	9 kgf (19.8 lbs)	2" (51 mm)	1-3/4" (45.2 mm)	2-5/16" (58.6 mm)	200
PXB-AS05-111-SD	Bronze Clear					

()units in mm

COAT HOOK (LEATHERY CHIC) PXB-LE05-111


STAINLESS



Black Tan Brown

• Modern design with contrasting materials.





No.	Part Name	Material	Finish
①	Head	ZDC	Black(BL) Brown(BR) Tan(TN)
②	Body		
③	Screw	304 Stainless Steel	
④	Pin	316 Stainless Steel	

Item No.	Color	Load Capacity	W	H	D	Weight (g)
PXB-LE05-111-BL	Black	25 lbs (11kgf)	1-13/16" (45.5)	1-13/16" (45.5)	2-5/8" (66)	267
PXB-LE05-111-BR	Brown					
PXB-LE05-111-TN	Tan					

()units in mm

FORGED BRASS DOUBLE HOOK

STEEL

PXB-BN05-211




- A high-end design which harmonizes both classical and contemporary styles.
- Built from luxurious solid brass forged to perfection.
- Meticulously crafted to ensure durability and a high quality finish.
- A clear lacquer coating is applied to prevent tarnishing.
- The endpoints feature a spherical design making it safer to use and lowers the risk of accidental injury.
- Includes screws that match the color of the finish.




Blasted Metal Polished Brass Satin Brass Antique Brass Matte Black





PXB-BN05-231



PXB-BN05-211

Item No.	Material	Finish	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
PXB-BN05-211-BM	Brass	Blasted Metal	18.7 lbs (8.5 kg)	165	4	20
PXB-BN05-211-PB		Polished Brass				
PXB-BN05-211-SB		Satin Brass				
PXB-BN05-211-AB		Antique Brass				
PXB-BN05-211-BL		Matte Black				
PXB-BN05-231-BM		Blasted Metal	33 lbs. (15 kg)	415		
PXB-BN05-231-PB		Polished Brass				
PXB-BN05-231-SB		Satin Brass				
PXB-BN05-231-AB		Antique Brass				
PXB-BN05-231-BL		Matte Black				

No.	Part Name	Material
①	Base	Brass
②	Arm	
③	Hex Socket Bolts	Steel


FORGED BRASS DOUBLE HOOK W/SWIVEL PXB-BNS05




Antique Brass Satin Brass Polished Brass Matte Black

- A solid, elegant brass hook that can swing 180°. The hook's friction feature prevents unintentional swinging due to vibration.
- A high-end design which harmonizes both classical and contemporary styles.
- Forged to perfection from luxurious solid brass.
- Meticulously crafted to ensure durability and a high quality finish.
- A clear lacquer coating is applied to prevent tarnishing.
- The endpoints feature a spherical design for safety and convenience.
- Includes screws that match the color of the finish.
- Hook can be securely tucked away when not in use.

180° Swing





No.	Part Name	Material
①	Base	Brass
②	Arm	
③	Shaft	304 Stainless Steel
④	Screws	-

Item No.	Finish	Material	Load Capacity	Weight (g)	Box (pcs)
PXB-BNS05-241-PB	Polished Brass	Brass	33 lbf (15 kgf)	680	1
PXB-BNS05-241-SB	Satin Brass				
PXB-BNS05-241-AB	Antique Brass				
PXB-BNS05-241-BL	Matte Black				

BALL HOOK

M4×25 STAINLESS

PXB-QC05-101

- No sharp corners for an elegant and safe design.
- The matte black finish is coated with a special chromate. This type combines the desirable glossiness of paint with the unique strength of plating.



PXB-QC05-101-BL




PXB-QC05-101-M



PXB-QC05-101-CR



PXB-QC05-101-GP



Item No.	Material	Finish/Color	A	Load Capacity	Weight (g)
PXB-QC05-101-CR	Zinc Alloy	Chrome Plating	3/16" (4.7 mm)	18 lbs (8.1 kg)	83
PXB-QC05-101-GP		24K Gold Plating			
PXB-QC05-101-BL		Chromate Finish/Matte Black			
PXB-QC05-101-M	Stainless Steel	Polished	1/8" (3 mm)	33.7 lbs (15.2 kg)	100

()units in mm

BALL HOOK

STAINLESS 304 STEEL

STAINLESS

PXB-QC05-111

- Mounting screws are not visible, giving a seamless look.
- No sharp corners for an elegant and safe design.
- The matte black finish is coated with a special chromate. This type combines the desirable glossiness of paint with the unique strength of plating.




PXB-QC05-111-CR





PXB-QC05-111-GP



PXB-QC05-111-BL







No.	Part Name	Material
①	Main Body	Zinc Alloy
②	Frame	
③	Hexagon Socket Set Screws	304 Stainless Steel
④		

Item No.	Material	Finish/Color	Load Capacity	Weight (g)
PXB-QC05-111-CR	Zinc Alloy	Chrome Plating	22.4 lbs (10.2 kg)	198
PXB-QC05-111-GP		24K Gold Plating		
PXB-QC05-111-BL		Chromate Finish/Matte Black		

BALL HOOK

STEEL

PXB-QL05-111

- Concealed mounting screws give a seamless look.
- No sharp corners for an elegant and safe design.
- The matte black finish is coated with a special chromate. This type combines the desirable glossiness of paint with the unique strength of plating.




PXB-QL05-111-CR



PXB-QL05-111-GP



PXB-QL05-111-BL



No.	Part Name	Material	Finish
①	Base	Zinc Alloy	Trivalent Chromate Finish
②	Base Cover		See table below
③	Arm		
④	Ball		
⑤	Hexagon Socket Set Screws	Steel	Trivalent Chromate Finish
⑥	Cross-Recessed Flat Head Screws		

Item No.	Material	Finish	Load Capacity	Weight
PXB-QL05-111-CR	Zinc Alloy	Chrome Plating	22.5 lbs (10.2 kg)	160g
PXB-QL05-111-GP		24K Gold Plating		
PXB-QL05-111-BL		Chromate Finish/Matte Black		

HOOK (WOOD CHIC SERIES)

STAINLESS 304 STEEL

STAINLESS

PXB-WC05-111

- Modern design with contrasting materials.
- Base is made from metal for a high loading capacity.
- The matte black finish is coated with a special chromate. This type combines the desirable glossiness of paint with the unique strength of plating.
- Product is made from natural wood. Grain and color may vary.




Hard Maple



Cherry



Walnut



No.	Part Name	Material	Finish
①	Wooden Part	Natural wood	Clear Coating
②	Plate	Zinc Alloy	See the table
③	Frame		Gloss Chromate Finish
④	Size M4 x 6 Hexagon Socket Set Screws	304 Stainless Steel	Plain

Item No.	Color (Wood)	Finish/Colour (Plate)	Load Capacity	Weight
PXB-WC05-111-HM	Hard Maple	Dull Nickel Plating	22.5 lbs (10.2 kg)	159g
PXB-WC05-111-CH	Cherry	Brass Plating/Vintage Look		157g
PXB-WC05-111-WN	Walnut	Chromate Finish/Matte Black		156g

HOOK

STEEL **HK-FH**



Black



Copper




Brass



Chrome

- Decorative contemporary hook.
- Available in four finishes and two sizes.



Item No.	Material	Finish	D	d_1	d_2	H	H_1	H_2	P	t	W	W_1	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
HK-FH30-CR	Zinc Alloy	Chrome	1" (25 mm)	3/16" (4.5 mm)	5/16" (8.6 mm)	1-3/16" (30 mm)	1/2" (12 mm)	1/4" (7 mm)	15/16" (23 mm)	3/16" (5 mm)	1-5/16" (34 mm)	3/8" (9 mm)	22 lb (10 kg)	22	25	300
HK-FH30-BL		Black														
HK-FH30-DB		Copper														
HK-FH30-PB		Brass														
HK-FH50-CR		Chrome	1-9/16" (39 mm)	3/16" (5.3 mm)	7/16" (10.6 mm)	1-3/4" (45 mm)	5/8" (16 mm)	3/8" (9.5 mm)	1-5/16" (34 mm)	1/4" (7 mm)	2" (50 mm)	1/2" (13 mm)	33 lb (15 kg)	65	15	200
HK-FH50-BL		Black														
HK-FH50-DB		Copper														
HK-FH50-PB		Brass														


()units in mm

HOOK

STAINLESS STAINLESS 316 STEEL **HK-LB**



- A stainless steel hook with a thick plate for a high-end look.
- Rounded hook tip to ensure safety.



Item No.	Material	Finish	W	H1	H2	P	A	B	C	D	t	Load Capacity	Weight (g)
HK-LB50	316 Stainless Steel	Polished	5/8" (16 mm)	2-9/16" (65 mm)	1-1/4" (32 mm)	2" (50 mm)	5/16" (8 mm)	5/8" (16.5 mm)	5/16" (8 mm)	1-9/16" (39.5 mm)	3/16" (5 mm)	33.7 lbs (15.3 kgf)	46
HK-LB65			11/16" (18 mm)	3-3/8" (85 mm)	1-3/4" (44.5 mm)	2-9/16" (65 mm)	3/8" (9 mm)	13/16" (20 mm)	3/8" (9 mm)	1-15/16" (49 mm)	1/4" (6.5 mm)		81

()units in mm