HIGH TEMPERATURE MAGNETIC CATCH — MC-YN005HP

NSF COMPONENT · RoHS compliant · STAINLESS 430 STEEL · STAINLESS 304 STEEL · NO SCREW

- Suitable for high temperature environments up to 250°C (482°F).
- Optional counterplates:
  - MC-JM49
  - AS-68



No.	Part Name	Material	Finish/Color
①	Yoke	430 Stainless Steel	Plain
②	Magnet	Samarium Cobalt	-
③	Housing	304 Stainless Steel	Plain
④	Center Yoke	430 Stainless Steel	

Item No.	Magnetic Force	Weight (g)	Box (pcs)	Carton (pcs)
MC-YN005HP-20	4.4 lbs (2.2 kg)	11	200	1000
MC-YN005HP-50	11.0 lbs (5.1 kg)			

HIGH TEMPERATURE MAGNETIC CATCH — MC0083HP

NSF COMPONENT · RoHS compliant · STAINLESS 430 STEEL · STAINLESS 304 STEEL · NO SCREW

- Suitable for high temperature environments up to 250°C (482°F).
- Strong magnetic force.
- Optional counterplates:
  - MC-JM49
  - AS-68



No.	Part Name	Material	Finish/Color
①	Housing	304 Stainless Steel	Plain
②	Magnet	Samarium Cobalt	-
③	Yoke	430 Stainless Steel	Plain

Item No.	Magnetic Force (kg)	Weight (g)	Box (pcs)	Carton (pcs)
MC0083HP-70	15 lbs (7 kg)	40	40	400
MC0083HP-140	31 lbs (14 kg)			