# LIFT-OFF HINGE

RoHS compliant | STAINLESS 304 STEEL | NO SCREW

## NH-40

• Left and Right handed available.



Left Right




| Item No. | | Weight (g) | Box (pcs) | Carton (pcs) |
|---|---|---|---|---|
| Left | Right | | | |
| NH-40L/SS | NH-40R/SS | 21 | 150 | 600 |

| Material | Finish |
|---|---|
| 304 Stainless Steel | Polished |

# LIFT-OFF HINGE

RoHS compliant | STAINLESS 304 STEEL | NO SCREW

## KN

• Left and Right handed available.



Left Right




| Material | Finish |
|---|---|
| 304 Stainless Steel | Polished |

| Item No. | | H | W | P1 | P2 | P3 | D1 | D2 | d | t | Weight (g) | Box (pcs) | Carton (pcs) |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| Left | Right | | | | | | | | | | | | |
| KN-50L/SS | KN-50R/SS | 2" (50 mm) | 1-1/4" (32 mm) | 3/16" (5 mm) | 13/16" (20 mm) | 13/16" (21 mm) | 5/16" (7.5 mm) | 3/16" (4 mm) | 1/8" (3.2 mm) | 1/16" (1.5 mm) | 32 | 100 | 400 |
| KN-64L/SS | KN-64R/SS | 2-1/2" (64 mm) | 1-7/16" (36 mm) | 5/16" (8 mm) | 15/16" (24 mm) | 15/16" (24 mm) | | | | | 44 | | |
| KN-75L/SS | KN-75R/SS | 2-15/16" (75 mm) | 1-1/2" (38 mm) | 5/16" (7.5 mm) | 1-3/16" (30 mm) | | 5/16" (8.5 mm) | | | 1/16" (2 mm) | 64 | 50 | 200 |