



Item No.			Material	Finish/Color	L ₁	L ₂	C
Exterior	Interior	Back-to-Back					
ZL-1506-OS-192	ZL-1506-IS-192	ZL-1506-WR-192	316 Stainless Steel	Zwei L	9-5/16" (237)	10-1/16" (256)	7-9/16" (192)
ZL-1506-OS-320	ZL-1506-IS-320	ZL-1506-WR-320			14-3/8" (365)	15-1/8" (384)	12-5/8" (320)
ZL-1506-OS-640	ZL-1506-IS-640	ZL-1506-WR-640			27" (685)	27-3/4" (704)	25-3/16" (640 mm)
ZL-1506-OS-960	ZL-1506-IS-960	ZL-1506-WR-960			39-9/16" (1005)	40-5/16" (1024)	37-13/16" (960)

()units in mm

Working Diagram		Door Thickness	Door Hole	Item No.	
Back-to-Back on Glass Door	With Base Plate		1/4"~9/16" (6~15 mm)	ø 5/8" (16 mm)	ZL-1506-WR
Back-to-Back on Wooden/Metal Frame Door	With Base Plate		1"~1-3/4" (25~45 mm)	ø 3/8" (9 mm)	ZL-1506-WR
	Without Base Plate		1-7/16"~2-1/4" (37~57 mm)	ø 3/8" (9 mm)	ZL-1506-WR
Single use on Wooden/Metal Frame Door	With Base Plate		Screws not included	ø 3/8" (9 mm)	ZL-1506-OS
				-	ZL-1506-IS
	Without Base Plate			ø 3/8" (9 mm)	ZL-1506-OS
				-	ZL-1506-IS

*If door thickness exceeds recommended thickness, a longer bolt (not supplied) should be used.