LAMP

HES INSTALLATION MANUAL FOR HES3D-120 CONCEALED HINGE (3-DIMENSIONAL ADJUSTABLE HINGE)

Read all instructions carefully for proper use.

↑ WARNINGS

- For indoor use only. Not suitable for areas where it can be in direct contact with water.
- · Use in conjunction with a door closer is not recommended. For soft-close option, we recommend Sugatsune LDD-V or LDD-S door damper.
- · Regarding usage with other types of concealed door closers we recommend using the hinge HES3D-160 instead.



Front / back

COMPONENT PARTS

HINGE PARTS

- CONCEALED HINGE 2 pcs
- Screw Cover 2 pcs.ea. (Door side, Frame side)

4 pcs× 2

- Flat Head Screw (5× 20)
- Hex Key (Key size 3)
- Template 1 pc
- INSTALLATION MANUAL

ITEM NO. / FINISH


ITEM NO.	FINISH
HES3D-120DC	Dull Chrome
HES3D-120DN	Dull Nickel
HES3D-120BL	Black


DOOR SPECIFICATIONS

Recommended door dimensions :		
Maximum Door Weight	Maximum Door Waight	30kg (66lbs) per 2 hinges
	40kg (88lbs) per 3 hinges	
	Minimum Door Thickness	29mm (1-9/64)
	Maximum Door Height	2400mm (94)
	Maximum Door Width	900mm (36)

ADJUSTMENTS

Vertical adjustment	± 2.5mm
Horizontal adjustment	± 2mm
Front / back adjustment	± 1mm






CUT OUT DRAWING

△Caution ·

Round edges of door and frame by applying cuts with "C1 and over" or "R1 and over." (Reference to *" in the drawing.)



Cut out drawing for door side

Cut out drawing for frame side

