Installation Manual ALT-ST15-D10




POCKET DOOR SYSTEM (OVERLAY) SOFT CLOSING

Thank you for selecting our product. Before starting installation, please read this manual thoroughly to ensure correct installation. Please keep this manual at hand for future reference.

ABOUT THE PRODUCT

- This product is hardware for vertical pocket doors in furniture, enabling slow door closing.
- The door is stored inside the cabinet.
- The door incline can be easily adjusted via a 5-stage angle retention mechanism.

Item Name Guide



SPECIFICATION

Туре	S	M	L	LL
Rail Q'ty	2	2	4	4
Door Width	Max.600[24"]			
Door Height	500 - 700 [19-11/16" - 27-9/16"]	700 - 900 [27-9/16" - 35-7/16"]	900 - 1200 [35-7/16" - 47-1/4"]	1200 - 1600 [47-1/4" - 63"]
Door Thickness	18 - 20[23/32" - 25/32"]			
Door Weight	Max. 9 kg [19.8 lbs]	Max. 9 kg [19.8 lbs]	Max. 15 kg [33 lbs]	Max. 15 kg [33 lbs]



Caution





Caution

If not followed, injury or damage may result.

- Provide a cabinet that can withstand the weight and impact of opening and closing the door. Be sure to use the specified screws and tighten them securely. If the mounting strength is insufficient, the door may fall and can cause injury.
- Follow the specified dimensions, specifications, and alignment of the cabinet. Make sure that the cabinet is not warped, since it may affect the movement of the door.
- Position the handle so that the hand holding the handle does not strike the side board.
- When moving the cabinet, remove the door and re-assemble it at the site.
- This product is a part for furniture. After installation, check the function and safety of the final product.
- Make sure to check the screws for slack at regular intervals. (one month and six months from first usage and then once every year is recommended).
 - · Be sure to inform users of the precautions below regarding opening and closing.
 - O Do not force the door to open past Damage may result.
 - When closing the door, pull it out until the catch clicks and then close it.
 - Repeated opening and closing may cause the inner rail to disconnect, shortening the door movement distance. Push the door fully inward or pull it fully out to correct the deviation.


				Overlay (ST15-D10)			
				S Type	M Type	L Type	LL Type
	1	Rail*	AL80C 16 - 28 in	2	2	4	4
	2	Connecting plate	ALT-ST15-S ALT-ST15-M ALT-ST15-L ALT-ST15-LL	1	1	1	1
	3	Concealed hinge	SCAF-7G99	2	2	3	3
	4	Hinge mounting plate	SBAR3R	2	2	3	3
	5	Mounting plate	ALT-MP32	2	2	3	3
	6	Damper Unit	SD0S8SNG	1	1	1	1
	7	Damper Base	SDARX99	1	1	1	1
	8	Door Stopper	ALT-ADS	2	2	3	3
	9	Protector	ALT-ADP	2	2	2	2
	10	Catch	AL127-CH	2	2	3	3
	11	Roller	DU19-B4SBR	2	2	2	2
	10	Roller Bracket	ALT-2V-AB	1	1	1	1
	12		ALT-2V-BB	1	1	1	1
	13	Insert Nut	SC-107-13	2	2	2	2
	14	Slider	G-175	2	2	2	2
	15	ALT-AB M5 Adjustment bolt		1	1	2	2
	16	Bind head tapping screw 3.5×15		20	20	36	36
arts Set	17	Bind head tapping screw 4×16		6	6	6	6
Pa	18	Raised countersunk head tapping screw 3.5×15	y	4	4	6	6
	19	Hexagon flange head screw M4×6		4	4	8	8
	20	Hexagon flange head screw M4×8		4	4	8	8
	21	Low countersunk head screw M4×8		2	2	3	3
	22	Raised countersunk head screw M4×10		4	4	6	6
	23	Raised countersunk head screw M4×	14	1	1	1	1
	24	Hex key	,	1	1	1	1

^{**} This catch holds the door at the pulled-out position. Be sure to mount it on the uppermost and lower slide rails (For details, see P.43).

1


Surface Mount

■ If Bottom Mount Bracket - Roller Bracket (12)



Position Roller Bracket as shown below:


Top View of Cabinet



Front of Cabinet


Flush Mount

■ Roller Guide Only




Position Insert Nut as shown below:

Top View of Cabinet



Side Mount

■ Side Board Installation




NOTE: Optional Side Mounting Bracket Sold Separately

> Requires a larger reveal: Top 15[19/32"] Bottom 15[19/32"]


Go to: "Step 2: Side Board Installation"

2 ■ Side Board Installation




Item Name	Installation Position
ALT - 2V5BR1	For Lower Right and Upper Left
ALT - 2V5BR2	For Upper Right and Lower Left


Section a-a



Note: Slider should always be installed towards front of the cabinet.










See next page for Rail Placement Drawings


4 Install Slide Rails & Guide Roller 1/2(Fix the only top slide rail and temporarily fix all other slide rails).





SUGATSUNE
















Mount the damper base and damper unit in the specified position.


Туре	S	М	L	LL
Hinge mounting plate Q'ty	2	2	3	3
Damper base	7	7		4
Mounting location				₹
[■ part]				

6 Mount Assembled Connecting Bar to Slide Rails




Fixing all other slide rails 2/2








Concealed hinge: SCAF-7G99













Simply line up hinge over the mounting plate and press down










- 10 Adjusting The Angle of the Door
 - 1 Loosen the screws fixing the connecting plate and the adjustment bolts. (After tightening, loosen 90° 180°)
 - Lift the door and shift the adjustment bolt backward one level at a time, to make the door and connecting plate vertical.
 5-stage adjustment is possible in accordance with the door weight.
 *When there are adjustment bolts at top and bottom, align their positions.



② Connecting plate








Adjustment bolt


3 Tighten all the screws once the door is in the desired position.












Closing speed adjustment (3 stages)



SUGATSUNE KOGYO CO., LTD. Tokyo, JAPAN Phone: +81 3 3866 2260 E-mail:export@sugatsune.co.jp

SUGATSUNE KOGYO (UK) LIMITED Reading, UK Phone: +44 1189 272 955 E-mail:sales@sugatsune.co.uk

SUGATSUNE EUROPE GmbH Düsseldorf, GERMANY Phone: +49 211 53812 900 E-mail:sales@sugatsune.eu

SUGATSUNE AMERICA, INC. California, USA Phone: +1 310 329 6373 E-mail:sales@sugatsune.com

Chicago, USA Phone: +1 630 317 7072 E-mail:sales@sugatsune.com

SUGATSUNE CANADA, INC. Montreal, CANADA
Phone: +1 514 312 5267
E-mail:support@sugatsune.ca

SUGATSUNE SHANGHAI CO., LTD. Shanghai, CHINA Phone: +86 21 3632 1858 E-mail:lamp@sugatsune.com.cn

Guangzhou, CHINA Phone: +86 20 6639 3554 E-mail:lamp@sugatsune.com.cn

SUGATSUNE KOREA CO., LTD. Incheon, KOREA
Phone: +82 32 220 0603
E-mail:sales@sugatsune-korea.co.kr

ISO9001(Japan Offices and Sugatsune America) and ISO14001(Chiba Production division and Logistics center), certified.

SUGATSUNE KOGYO INDIA PRIVATE LIMITED Mumbai, INDIA Phone: +91 9867299597

E-mail:sales@sugatsune.in

Delhi, INDIA Phone: +91 9867299597 +91 11 45093636 E-mail:sales@sugatsune.in



