

HES3D - V135 3D adjustable concealed hinge Installation Manual

PAT.P

For proper installation and your own safety, read this manual carefully and follow the instructions.

• The HES3D-V135 is a concealed hinge for indoor doors as specified below. Sugatsune declines responsibility for any malfunction, accident or injury caused by use others than originally intended for.

. The utmost care was taken during the production of this hinge. However, should you find any defects, please immediately contact your local retailer for replacement

· The Warranty period is one year after shipment date. Sugatsune's liability shall be limited to replacement of the product and will in no case extend to the assembly as a whole.

CAUTION:

! For indoors use only. Do not use in locations where it is in direct contact with water.

! Operation temperature range is -10°c ~40°c.


! When using a door closer, always test the final assembly. For soft-closing option, we recommend the use of the Sugatsune LDD-V door damper.

Parts list

· Concealed hinge: 2 pcs Frame side screw cover: 2 pcs / hinge Cutout template: 1


 Door side screw cover L and R: 1 set / hinge Fixing screws: 2 pcs / hinge Installation manual (this manual): Installation screws (cross recessed binding head tapping screws 5x15): 8 pcs / hinge


Door specifications Maximum door weight: 40 kg (2 hinges use) Minimum door thickness: 30 mm Maximum door width: 900 mm Maximum door height: 2400 mm





Cutout and installation drawings


*We recommend that you use the provided template for easier installation














Phone: +81 (0)3 3866 2260 Phone: +44 (0)1491 680737 F a x : +81 (0)3 3866 4447 Fax: +44 (0)1491 680762 E-mail: export@sugatsune.co.ip E-mail: sales@sugatsune.co.uk Website: www.sugatsune-intl.com Website: www.sugatsune.co.uk



Make sure that the height adjustment screws are set as shown on Fig. B and secure the frame base to the frame with 4 fixing screws

3. Insert the hinge body in the door cutout (Fig. C) and fasten securely using 4 fixing screws.

place.

5. Slightly tighten the fixing screws through the oval holes of the hinge body (FIG. C).

Door can be adjusted in all three dimensions (FIG D). Direction (+) or (-) is indicated near adjusting screw. 1.Vertical adjustment (±3 mm) Make sure fixing screws are only slightly tightened. Lift the door and adjust its height by turning the vertical adjustment screw (lower side), then firmly tighten all fixing

Turn the horizontal adjustment screw right (+) to increase and left (-) to decrease the gap between the side frame and the door.

Turn the depth adjustment screw left (+) for front and right (-) for back adjustment. Caution: DEPTH ADJUSTMENT MUST BE CARRIED OUT BY TURNING THE SCREWS IN TURN AND BIT BY BIT.

4. Additional tightening After adjustment, make sure that all fixing screws are securely tightened (recommended fastening torque is 1.5~2.0 Nm).

Attach covers on the hinge and frame side as shown on the hinge dimension drawing. Pay particular attention to the Left and Right covers for the door side. Caution: DO NOT APPLY EXCESSIVE FORCE WHEN INSTALLING OR REMOVING THE COVERS.

Installation Procedure

1.Separate the hinge body marked as "Door Side", from the frame base marked as "Frame Side" (FIG. A).

2.Insert the frame base in the frame cutout. Height adjustment screws should be closer to the frame reference side (Fig. C).

4. Turn the hinge body as shown on Fig. C and insert the hinges body completely in the frame bases simultaneously at the top and bottom. By lowering the door slowly in that position, the door should be held in

Caution: DO NOT MOVE THE DOOR AT THIS STAGE AS IT MAY FALL OFF.

Caution: ONLY OPEN OR CLOSE THE DOOR CAREFULLY AS IT IS NOT PROPERLY SECURED AT THIS STAGE.

Adjustment Procedure

Adjustment directions shown in Fig. D are the ones when the door is closed.

screws. Lastly, move the vertical adjustment screw (upper side)

to the inner direction so that it touches the hinge body.

2. Horizontal adjustment (+2 mm - 1.5 mm)

Caution: DO NOT UNSCREW THE ADJUSTMENT SCREW COMPLETELY AS THE DOOR MAY FALL OFF.

3. Depth adjustment (+1 mm -4 mm)

Cover installation

SUGATSUNE AMERICA, INC. Phone: +1 310 329 6373 F a x : +1 310 329 0819 E-mail: sales@sugatsune.com Website: www.sugatsune.com

SUGATSUNE SHANGHAI CO., LTD. Phone: +86 (0)21 3632 1858 F a x : +86 (0)21 3632 1868 E-mail: lamp@sugatsune.com.cn Website: www.sugatsune.com.cn

ISO9001(Japan offices only)and ISO14001(Chiba production division and Logistic center only)certified.