


SURFACE MOUNT SLIDING DOOR HARDWARE (Door Weight 200 lbs) SDR-RA80-SM



Type	SDR-RA80-SM	
	Surface Mount Sliding Door	
Roller	Top Surfaced	
Track Mounting	Ceiling	Wall w/Continuous Bracket
Door Weight	Max. 200lbs (90 kg)	
Door Thickness	Min. 1-1/8" (28 mm)	
Door Width	Two-Way Soft Close Min. 33-7/16" (850 mm) Standard Close Min. 25-9/16" (650 mm)	



- 200lbs (90kg)
- Ceiling and Barn Door Mount
- Surface Mounted door brackets
- Double rollers with ball bearings
- Quiet precision movement
- Soft Close Feature
- Vertical Adjustment $\pm 1/16"$ (1mm)

How to order

1. Select track and track length
 - 1A. Select any optional parts for track
2. Choose a hardware set (dual soft closing or standard)

Ordering Information

1. Track Options

Track Type	Length	Item No.	Description
Standard Aluminum Track	78-3/4" (2000 mm)	SDR-RA80-2000	
	118-1/8" (3000 mm)	SDR-RA80-3000	
False Ceiling Aluminum Track	78-3/4" (2000 mm)	SDR-RA80-TC-2000	



1A Optional Parts for Track

 SDR-RA80WL-2000 SDR-RA80WL-3000 Wall Mount Bracket	 SDR-RA80-8083 End Cover for Track	 SDR-RA80-8085 End Cover for Track & Wall Mount Bracket
---	---	---


2. Hardware Set

Closing Feature	Item No.	Set Details
Dual Soft Close	SDR-RA80-SM-DSC	 (1) SDR-RA80-SM-KIT Surface Mount Brackets + (2) SDR-RA80-8006 Soft Close Rollers
Standard Closing	SDR-RA80-SM-RR	 (1) SDR-RA80-SM-KIT Surface Mount Brackets + (2) SDR-RA80-8080 Standard Rollers


TRACK MOUNTING OPTIONS




Traditional ceiling mount option shown.



For a clean and seamless look, the continuous bracket will run the full length of the track.



Two-Way Soft Close



Standard Closing

