3-WAY ADJUSTABLE CONCEALED HINGE

HINGES




28

SUGATSUNE

- · 3-WAY adjustment function allows vertical, horizontal, and depth adjustment after hinge installed.
- · Easy installation with LIFT-OFF FEATURE: can be split into two parts (one for the frame and one for the flap), can temporarily be hung and hold position without being affixed with screws.
- · Successfully passed 300,000 open/close private cycle tests. · UL Rated, up to 3 Hours
- · Supplied with steel flat head screw.
- · Covers hide all screw heads for clean appearance.
- Door weight : Max. 100 kg (220 lbs)/2 pcs, 125 kg (275 lbs)/3 pcs.
- Door Thickness : Min. 38 mm (1-1/2").
- Max. Door Size : H 2400 mm (94-1/2") × W 914 mm (36").
- · Bracket for sheet metal doors and frames available (sold separately). Metal cover plates available for Polished Nickel (PN) finish
- HES3D-E190PN-CM (sold seprately).

Max.6.5



Item No.	Weight (g)	Box (pcs)	Carton (pcs)
HES3D-E190PN-UL			
HES3D-E190DC-UL			
HES3D-E190DN-UL	1050	2	12
HES3D-E190BL-UL			
HES3D-E190WT-UL			


HES3D-E190BL-UL

HES3D-E190WT-UL

HES3D-E190

IS

RoHS



No.	Part Name	Material	Finish/Color
1	Body	Zinc Alloy	Polished Nickel (PN) Dull Chrome (DC) Dull Nickel (DN) Matte Black (BL) White (WT)
2	Base Frame	Zinc Alloy	Polished Nickel (PN) Dull Chrome (DC) Dull Nickel (DN) Matte Black (BL) White (WT)
3	Arm	Aluminum Alloy	Polished Nickel (PN) Dull Chrome (DC) Dull Nickel (DN) Matte Black (BL) White (WT)
4	Pin	304 Stainless Steel	-
6	Cover	ABS	Polished Nickel (PN) Dull Chrome (DC) Dull Nickel (DN) Matte Black (BL) White (WT)

1-800-562-5267 (U.S.A. Only)