


HOOK



XL-HJT



- 304 stainless steel hooks.
- Available in Mirror (M) or Combination of Mirror and Satin (TT) finish.


Item No.	D	W	H	H ₁	P ₁	P ₂	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
XL-HJT-55/M	33	15.0	55	23	8	19	20 (44.0 lbs)	34	30	300
XL-HJT-55/TT		15.5								
XL-HJT-70/M	43	18.0	70	30	10	23	15 (33.0 lbs)	53	20	200
XL-HJT-70/TT		18.5								

Material	Finish	
	M	TT
304 Stainless Steel	Mirror	Mirror and Satin Combination

HOOK



HJT



- 4mm thick material designed for excellent durability.


Item No.	D	H	H ₁	t	W	C ₁	C ₂	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
HJT-55	33	55	23	4	15	8	19	10 (22.0 lbs)	34	30	300
HJT-70	43	70	30	4	18	10	23	8 (17.6 lbs)	53	20	200

Material	Finish
304 Stainless Steel	Satin

FORK HOOK



EU



- Hook with unique design.
- Can hang 3 items at the same time: two on the tips and one on the neck.
- Two-tip shape ideal to hang hats, caps etc.

Item No.	W ₁	(W ₂)	D ₁	D ₂	(D ₃)	D ₄	H ₁	H ₂	d	d ₁	P ₁	P ₂
EU-50	22	38 (1-1/2")	38 (1-1/2")	4	17.8	5	50 (1-31/32")	9	4	7.4	7	20
EU-72	32	56 (2-13/64")	52 (2-3/64")	6	23.0	8	72 (2-53/64")	14	4.6	8.6	10	34

Item No.	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
EU-50	20 (44 lbs)	42	20	120
EU-72	30 (66 lbs)	118	10	60

Material	Finish
316 Stainless Steel	Mirror