


# MAGNETIC CATCH


**MC0097**


MC0097/WHT



MC0097/BLK



| No. | Part Name    | Material     | Finish/Color |
|-----|--------------|--------------|--------------|
| ①   | Housing      | Polyethylene | Black/White  |
| ②   | Yoke         | Steel        | Chromate     |
| ③   | Magnet       | Ferrite      | -            |
| ④   | Counterplate | Steel        | Chromate     |

| Item No.     |              | Magnetic Force (kg) | Weight (g) | Box (pcs) | Carton (pcs) |
|--------------|--------------|---------------------|------------|-----------|--------------|
| White        | Black        |                     |            |           |              |
| MC0097/WHT   | MC0097/BLK   | 1.5 (3.3 lbs)       | 12         | 100       | 1000         |
| MC0097/WHT-1 | MC0097/BLK-1 | 3.5 (7.7 lbs)       |            |           |              |


# MAGNETIC CATCH


**MC-84**


MC-84/IVY



MC-84/BLK





• Adjustable magnet position (5.5 mm)

| No. | Part Name    | Material | Finish/Color             |
|-----|--------------|----------|--------------------------|
| ①   | Housing      | ABS      | Black (BLK), Ivory (IVY) |
| ②   | Yoke         | Steel    | Bronze/Nickel            |
| ③   | Magnet       | Ferrite  | -                        |
| ④   | Screw        | Steel    | Bronze/Nickel            |
| ⑤   | Counterplate |          |                          |

| Item No.  | Magnetic Force (kg) | Weight (g) | Box (pcs) | Carton (pcs) |
|-----------|---------------------|------------|-----------|--------------|
| MC-84/IVY | 3 (6.6 lbs)         | 18         | 50        | 1000         |
| MC-84/BLK |                     |            |           |              |


# MAGNETIC CATCH


**SUPER-78**


| No. | Part Name    | Material | Finish/Color          |
|-----|--------------|----------|-----------------------|
| ①   | Housing      | Aluminum | Brown Baked Lacquered |
| ②   | Yoke         | Steel    | Chromate              |
| ③   | Magnet       | Ferrite  | -                     |
| ④   | Counterplate | Steel    | Chromate              |

| Item No. | Magnetic Force (kg) | Weight (g) | Box (pcs) | Carton (pcs) |
|----------|---------------------|------------|-----------|--------------|
| SUPER-78 | 0.8 (1.7 lbs)       | 17         | 36        | 720          |

# MAGNETIC CATCH


**SUPER-88**


| No. | Part Name    | Material | Finish/Color |
|-----|--------------|----------|--------------|
| ①   | Housing      | Aluminum | Anodized     |
| ②   | Yoke         | Steel    | Chromate     |
| ③   | Magnet       | Ferrite  | -            |
| ④   | Counterplate | Steel    | Chromate     |

| Item No. | Magnetic Force (kg) | Weight (g) | Box (pcs) | Carton (pcs) |
|----------|---------------------|------------|-----------|--------------|
| SUPER-88 | 1.5 (3.3 lbs)       | 28.5       | 24        | 720          |