


PIANO HINGE



LSD-30

- Double folded construction provides extra rigidity.
- The knuckles on both ends are crimped to prevent the pin from being removed. The hinge pin does not occupy the crimped knuckles on both ends.




Material	Finish
304 Stainless Steel	Satin

Item No.	L	B	C	C ₁	C ₂	t	S	Holes	Weight (g)	Box (pcs)	Carton (pcs)
LSD-30-240	240 (9-29/64")	30 (1-3/16")	10.5	43.5	17	1.2	3.5	12	65	20	200
LSD-30-300	300 (11-13/16")			46.3				14	80		
LSD-30-360	360 (14-11/64")		15.0	47.0				16	95		
LSD-30-450	450 (17-23/32")		14.5	60.0				16	120		
LSD-30-600	600 (23-5/8")		14.0	63.3				20	190		
LSD-30-900	900 (35-7/16")			62.3				30	280		

PIANO HINGE (WELD-ON)



LSN



Item No.	L ₁	L ₂	W	t	D	Weight (g)	Box (pcs)	Carton (pcs)
LSN 8-25- 300	300 (11-13/16")	12.5	25 (63/64")	0.8	2.6	66	20	200
LSN 8-25- 600	600 (23-5/8")					135		
LSN 8-25-1000	1000 (39-3/8")					222		
LSN 8-25-1800	1800 (70-55/64")		400					
LSN 8-32- 300	300 (11-13/16")		32 (1-17/64")			80		
LSN 8-32- 600	600 (23-5/8")					159		
LSN 8-32-1000	1000 (39-3/8")	272						
LSN 8-32-1800	1800 (70-55/64")	38 (1-1/2")	492					
LSN 8-38-1000	1000 (39-3/8")		289					
LSN 8-38-1800	1800 (70-55/64")		542					
LSN15-32- 300	300 (11-13/16")	20.0	32 (1-17/64")	1.5	3.5	78	10	100
LSN15-32- 350	350 (13-25/32")					192		
LSN15-32- 450	450 (17-23/32")					248		
LSN15-32- 600	600 (23-5/8")					330		
LSN15-32- 750	750 (29-17/32")					410		
LSN15-32- 850	850 (33-15/32")					464		
LSN15-32- 900	900 (35-7/16")		498					
LSN15-32-1000	1000 (39-3/8")		574					
LSN15-38-1000	1000 (39-3/8")		38 (1-1/2")			615		
LSN15-38-1800	1800 (70-55/64")					1121		
LSN15-50-1000	1000 (39-3/8")					759		
LSN15-50-1800	1800 (70-55/64")		50 (1-31/32")			1367		
LSN20-50-1000	1000 (39-3/8")	50.0		2.0	5.0	774	5	50



Material	Finish
304 Stainless Steel	Satin