

GLASS DOOR CAM LOCK






1310GL

LOCKS



- Dimple key lock series ideal for showcase application.
- High security reversible key. (3 keys supplied)
- Key acts as a knob and can only be removed when locked.
- 1 million key changes available; please specify keyed alike or differently when ordering.
- Available in Satin Nickel (SN), Chrome (CR), Gold (GC) or Black Chrome (BL) finish.
- Master key system available at surcharge. (Max. 2,520 key changes per master key.)



Cut Out Dimension

Item No.	Glass Thickness	Weight (g)	Box (pcs)	Carton (pcs)
1310GL-SN	3/16"~5/16" (5~8)	139	12	60
1310GL-CR				
1310GL-GC				
1310GL-BL				

(units in mm)

No.	Part Name	Material	Finish			
			SN	CR	GC	BL
①	Body	Brass	Nickel	Chrome	Gold	Black Chrome
②	Ring					
③	Front Plate	304 Stainless Steel	Satin	Polished	Gold	Black Chrome
④	Cam				Plain	
⑤	Hex Nut				Silver	
⑥	Washer	Steel			Nickel	
⑦	Hex Nut				Silver	
⑧	Case Cover				Black	
⑨	Ring	Polypropylene				
⑩	Counterplate	303 Stainless Steel		Polished		Black Chrome
⑪	Key	Brass			Nickel	

GLASS DOOR CAM LOCKS




GLASS DOOR CAM LOCK FOR DOUBLE DOORS



1310GLW



- Dimple key lock series ideal for showcase application.
- High security reversible key. (3 keys supplied)
- Key acts as a knob and can only be removed when locked.
- 1 million key changes available; please specify keyed alike or differently when ordering.
- Master key system available at surcharge. (Max. 2,520 key changes per master key.)



Cut Out Dimensions

Item No.	Glass Thickness (mm)	Weight (g)	Box (pcs)	Carton (pcs)
1310GLW	5~8 (3/16"~5/16")	206	12	60

(units in mm)

No.	Part Name	Material	Finish
①	Body	Brass	Nickel
②	Ring		
③	Front Plate	304 Stainless Steel	Satin
④	Cam		Plain
⑤	Hex Nut		
⑥	Washer	Steel	Silver
⑦	Hex Nut		
⑧	Case Cover		
⑨	Ring	Polypropylene	Black
⑩	Counterplate	304 Stainless Steel	Polished
⑪	Key	Brass	Nickel
⑫	Backplate	304 Stainless Steel	Polished
⑬	Stopper	Polyamide	Brown