

# DOOR HANDLES AND APPLIANCE PULLS

HANDLES

DOOR HANDLES AND APPLIANCE PULLS



## Mounting Kit for DSI Series Door Handles

### Single handle installation kit for wood/glass/metal doors


Exterior  
Handle

Max. Door Thickness:

DSI-1630-30: 4" (100 mm)	DSI-3310-30: 2-3/8" (60 mm)
DSI-2000-20: 3-3/16" (80 mm)	DSI-3330-30: 4" (100 mm)
DSI-2000-30: 3-3/16" (80 mm)	DSI-4400-15: 2-3/8" (60 mm)
DSI-3310-15: 2-3/8" (60 mm)	DSI-4400-20: 2-3/8" (60 mm)
DSI-3310-20: 2-3/8" (60 mm)	DSI-4400-30: 2-3/8" (60 mm)

Item No.	For use with
DKIT-2/15-1	DSI-3310-15
DKIT-2/15-2	DSI-4400-15
DKIT-2/20-1	DSI-2000-20/DSI-3310-20
DKIT-2/20-2	DSI-4400-20
DKIT-2/30-1	DSI-1630-30/DSI-2000-30/DSI-3310-30/DSI-3330-30
DKIT-2/30-2	DSI-4400-30

### Back-to-back handle installation kit for wood/glass/metal doors


Exterior  
Handle

Max. Door Thickness:

DSI-1630-30: 3-1/2" (90 mm)	DSI-3310-30: 4" (100 mm)
DSI-2000-20: 4" (100 mm)	DSI-3330-30: 4" (100 mm)
DSI-2000-30: 1-3/4" (45 mm)	DSI-4400-15: 4" (100 mm)
DSI-3310-15: 4" (100 mm)	DSI-4400-20: 4" (100 mm)
DSI-3310-20: 4" (100 mm)	DSI-4400-30: 4" (100 mm)

Interior  
Handle

Item No.	For use with
DKIT-4/15-1	DSI-3310-15
DKIT-4/15-2	DSI-4400-15
DKIT-4/20-1	DSI-2000-20/DSI-3310-20
DKIT-4/20-2	DSI-4400-20
DKIT-4/30-1	DSI-1630-30/DSI-2000-30/DSI-3310-30/DSI-3330-30
DKIT-4/30-2	DSI-4400-30



### Single handle installation for concrete walls

Item No.	For use with
DKIT-5/15	DSI-3310-15/DSI-4400-15
DKIT-5/20	DSI-2000-20/DSI-3310-20/DSI-4400-20
DKIT-5/30	DSI-1630-30/DSI-2000-30/DSI-3310-30/DSI-3330-30/DSI-4400-30