

FOLDING DOOR SYSTEM

FD30-F

SLIDING & FOLDING DOOR HARDWARE

FOLDING DOOR SYSTEM (MAX. 33 LBS PER PANEL)



Item No.	FD30UKP	FD30URP	FD30UMP	FD30UP
Application	Standard Folding (One pivot fixed)	Slidable (for partition use)	Slidable (for cabinet use)	Swing Door
Door Width	Max. 450 mm (17-3/4")			
Door Height	Max. 2400 mm (94-1/2")			
Door Thickness	Min. 30 mm (1-3/16")			
Door Weight	Max. 15 kg (33 lbs) per door panel			

Parts Set (Per 2 doors)

Necessary Parts


Please refer to "Qty [a] ~ [d]" for parts included in each set.

	Item No.	Description
[a]	FD30UKP	Pivoted Folding, Center Hinge (Surface Mount)
[b]	FD30URP	Slidable Folding, Center Hinge (Door Edge Recessed Mount)
[c]	FD30UMP	Slidable Folding, Center Hinge (Back Side Recessed Mount)
[d]	FD30UP	Pivoted Swing open (Single Panel)

Parts Included

No.	Qty				Part Name / Item No.	Description
	a	b	c	d		
1	2 pcs	2 pcs	-	1 pc	Upper Roller (Recessed Type) FD30-WRH	• Material Zinc Alloy/Polyacetal • Finish Chromate/Light Brown
2	-	-	2 pcs	-	Upper Roller (Side-Mount) FD30-WRU	• Material Steel/Polyacetal • Finish Chromate/Brown
3	1 pc	-	-	-	Stopper Block FD30-HSB	• Material Polyacetal • Finish Dark Brown
4	1 pc	-	-	1 pc	Bottom Pin FD30-FBP	• Material Steel/Polyacetal • Finish Chromate/White
5	-	2 pcs	2 pcs	-	Guide Pin FD30-FGR	• Material Steel/Polyacetal • Finish Chromate/White
6	1 pc	1 pc	1 pc	1 pc	Pin Insert Jig FD30-FKPIJ	-
7	1 pc	-	-	1 pc	Spanner Wrench FD30-FSP	-
8	-	-	-	1 pc	Top Bracket FD30-FSK	• Material Steel • Finish Chromate

Configuration



No.	Qty				Part Name / Item No.	Description
	a	b	c	d		
9	1 pc	-	-	-	Pivot Bracket (Bottom) FD30-FPU	• Material Steel • Finish Chromate
10	1 pc	-	-	1 pc	Fixing Plate FD30-FKK	• Material Steel • Finish Chromate
11	-	2 pc	2 pc	-	Upper Stopper FD30-FTST	• Material Steel/Polyacetal • Finish Chromate/Brown
12	-	2 pc	2 pc	-	Bottom Stopper FD30-FBKS	• Material Steel/Polyacetal • Finish Chromate/Brown
13	-	-	-	1 pc	Magnetic Catch FD30-FMC	• Material Steel/ABS Plastic • Finish Chromate/Brown
14	3 pcs	-	-	-	Center Hinge (Surface Mount, Angle adjustable) FD30-CHM	• Material Steel • Finish Black
15	-	-	3 pcs	-	Center Hinge (Recess Mount, Angle adjustable, W/Detent Stop) FD30-CHH	• Material Steel • Finish Black
16	-	3 pcs	-	-	Center Hinge (Door Edge Mount, Angle adjustable, W/Detent Stop) FD30-CHK	• Material Zinc Alloy • Finish Dark Brown