

FOLDING BRACKETS

EB Series















- Automatically locks when flap is in open position. Press lever to release the lock.

 - Hinges not required.
 Damper unit with a soft-closing feature which makes it smoother and safer.
 Durability tested 50,000 cycles (private).
 Refer to the DAMPER WEIGHT CHART for damper


 - weight capacity.









FOLDING BRACKET with damper





Bracket Load Capacity P1 (kg)

150 (330 lbs)



		×
Part Name	Material	
Main Body	304	
Plate Spring	Stainless	1004
Rivet	Steel	Int

Bracket Load Capacity P2 (kg)	Weight (g)	Carton (pcs)
75 (165 lbc)	515	20



SUGATSUNE

SHELF & SUPPORT HARDWARE

Item No.

EB-303/EP-D

SUGATSUNE


DAMPER FOR EB FOLDING BRACKET

SHELF & SUPPORT HARDWARE












- Lapcon technology provides soft-close movement downward.
- Easy surface-mount installation.
- Ideal for counter flaps at bars, restaurants and receptions.







ABS/POM/Steel	Gray/Zinc/Chrome			Shelf board
Item No.	Toro	ue (kg·cm)	Thickness (mm) Min. Panel	Weight (g)
EBD	86.7~153.0	(75.3~132.8 lbs•in)	15	400

1-800-562-5267 (U.S.A. Only)

Box (pcs)

FOLDING BRACKET



SUGATSUNE
















- · Automatically locks when flap is in
- opened position.
 Press lever to release the lock.
 Bracket can be used without the need.
- blacket dan 25 for hinges.
 Available in 3 different sizes.
 Damper unit EBD available for use with all EB series brackets (sold separately).




Part Name		Material
	Main Body	
	Plate Spring	304 Stainless Steel
	Rivet	








www.sugatsune.com





Item No.	Load Capacity P1 (kg)	Load Capacity P2 (kg)	Weight (g)	Carton (pcs)
EB-200/EP	175 (385 lbs)	90 (198 lbs)	330	20
EB-303/EP	150 (330 lbs)	75 (165 lbs)	515	20
EB-317/EP	200 (440 lbs)	100 (220 lbs)	750	20

Carton (pcs)

www.sugatsune.com

Finish/Color

Material

477.4

LEVER RELEASE for EB Folding Bracket










No.	Part Name	Material	Finish
1	Connecting Lever	Aluminum	Anodized
2	Side Lever	Aluminum	Aluminum
3	Spring	Stainless Steel	Plain
4	Washer	Plastic	-
5	Holding Bracket	Aluminum	Anodized
6	Connecting Rod	Aluminum	Aluminum
7	Safety Lock Screw	Stainless Steel	Plain


No.	Part Name	Material	Finish
1	Connecting Lever	Aluminum	Anodized
2	Side Lever	Aluminum	Aluminum
3	Spring	Stainless Steel	Plain
4	Washer	Plastic	-
5	Holding Bracket	Aluminum	Anodized
6	Connecting Rod	Aldiffillulli	Aluminum
7	Safety Lock Screw	Stainless Steel	Plain




	for locking and lever release.
•	Lever can be used with either EB-303/EP, EB-303/
	EP-D, EB-200/EP or EB-317/EP.
•	Use to unlock multiple brackets with one-hand
	operation while maintaining bracket locking feature.
	Connecting har can be cut to sizes

•					
 Available for two or three 	ee brackets	s conf	igura	ıtioı	n.
 Corrosive resistant alu 	minum mat	terial a	allow	s fo	r
outdoor use.					

 Simple installation, easier support for wide shelves
 Ideal solution to save space in confined areas.





1-800-562-5267 (U.S.A. Only)

LEVER RELEASE for EB Folding Bracket






EB-1000-2/1500-2

Holding Bracket Qty

EB-2000-3



EB-1500-2	1	59-1/16" (1500 mm)	2	1	3	1


Side Lever Qty

Safety Lock Qty

Rod Length (L)

39-3/8" (1000 mm)

LEVER RELEASE for EB Folding Bracket



Item No. Rod Qty Rod Length (L) Side Lever Qty Connecting Lever Qty Safety Lock Qty Holding Bracket Qty Spring EB-2000-3 2 39-3/8" (1000 mm) each 2 1 1 6 1								
EB-2000-3 2 39-3/8" (1000 mm) each 2 1 1 6 1	Item No.	Rod Qty	Rod Length (L)	Side Lever Qty	Connecting Lever Qty	Safety Lock Qty	Holding Bracket Qty	Spring Qty
	EB-2000-3	2	39-3/8" (1000 mm) each	2	1	1	6	1

Item No.

EB-1000-2

Connecting Lever

Rod Qty





Chicago Showroom 121 West Wacker Drive Chicago, IL 60601







