

Adjustments







Adjustment screw (Vertical)


Loosen screw, adjust the door and retighten screw.



Leveling Adjustment Screw Front







SUGATSUNE KOGYO CO.,LTD.

Phone: +81 (0)3 3866 2260 Fax: +81 (0)3 3866 4447 E-mail: export@sugatsune.co.jp Website: www.sugatsune-intl.com

Back

SUGATSUNE KOGYO (UK) LTD. Phone: +44 (0)1491 680737 Fax: +44 (0)1491 60762

E-mail: sales@sugatsune.co.uk Website: www.sugatsune.co.uk

SUGATSUNE AMERICA, INC. Phone: +1 310 3296373

Fax: +1 310 3290819 E-mail: sales@sugatsune.com Website: www.sugatsune.com

SUGATSUNE SHANGHAI CO., LTD. Phone: +86 (0)21 3632 1858 Fax: +86 (0)21 3632 1868 E-mail: lamp@sugatsune.com.cn

Website: www.sugatsune.com.cn 2009.05 PRINTED IN JAPAN 0445-1






MonoFlat LIN-X hinge TM

MonoFlat LIN-X 450 Instruction Manual PAT.P

Thank you for purchasing this MonoFlat LIN-X hinge by SUGATSUNE. Before proceeding with the installation, please read this instruction manual carefully for the best possible result and ensure your safety.



!\WARNING:

- Failure to observe the following precautions may result in injury and/or lead to damage to surrounding cabinets or fittings.
- Choose suitable screws to ensure of proper installation of the cabinet and door.
- Ensure that door size, weight and material correspond to the specifications stated in this
- Do not disassemble or modify the system.

■ Product Specification


Door width	400∼500 mm			
Door height	600~900 mm			
Door thickness	15~24 mm			
Door weight	Max 7 kg (per door)			

■Parts List

①LIN-X Body · · · · · 2 pcs.		②Mounting Plate······ 2 pcs.			③Connecting plate · · · · · 1 pc.		
					3	L=540m	
(Connecting plate Cover	⑤ Cup	Cover	Countersunk head tapping screw		pping screw	Binding & tapping screw
	2 pcs.	2 pcs.		3.5×15 ····· 6 pcs.			3.5×15 ····· 8 pcs.


■Overall (unit: mm)

• Picture shows the left hand door use. (Right hand door use is symmetrical.)




■Overlay distance


- Side overlay as shown in Fig. 1 is:
 19 mm for mounting plate 230-P4W-32T
 14 mm for mounting plate 230-P4W-32T+5
- An opening clearance of 2mm is required on both sides of the door.



■Position of LIN-X Body


• Prepare the door as per Fig. 2 and Fig. 3






■Mounting Plate Position

 Prepare the sideboard for mounting plate installation as Fig. 4




■Installation

1 Mounting plate installation:





2 Cup Cover installation:



Ensure that the two o are pointing toward the edge of the door.


3 LIN-X body installation:






Ensure that the two LIN-X bodies are parallel by measuring both the base and mounting plate distances.

4 Connecting plate installation:



5 Door installation:



Ensure that the LIN-X body is securely attached to the mounting plates.



