

Premium Hardware for Food Service & Convenience Stores



Lid Supports



Heavy Duty Lift-Assist Damper Can hold up to 36 lbs/each. Available in Brown and White.



LAD

A Compact soft down damper. Ideal for lighter bar top applications.



For downward-opening flap doors. Can be installed individually or in pairs. Non-Handed: left or right side.



S-AT01, S-AT02

Back and side panel mounting, Spring mechanism assisting in lifting door and holds in open position.

Multi-Purpose Lids & Grommets



AZ-GD231-HL

Rectangular stainless steel multi purpose lid w/ soft close. Available in various sizes.



AD-GD

Round stainless steel multi purpose lid w/ soft close. Available in various sizes. Also available in squares.



AN-DH

Round stainless steel grommet. Available in various sizes, depths and finishes.




AN-KH

Square stainless steel grommet. Available in various sizes and depths.





SAM/SAD Stainless steel, round and oblong shaped 0.4mm diameter mesh wired ventilator.



Catches & Latches





MC-MSH Silicone sealed neodymium mag. catch. Avoids meta-to-metal





MC-YN005HP

Stainless steel, suitable for high temperatures up to 482°F. Available in 4.4 and 11 lbs magnetic force.





BCTS Made of high grade 316 Stainless steel tension catch. Available in 3 sizes.



ESN-195-3.1

Non-magnetic push latch with strong retaining force.





KR-50

Stainless steel slide bolt.



FL2

Stainless steel compact slide bolt.

Hinges





A Gravity Hinge with lift-off function, up to 44 lbs load capacity and

built-in soft-close after 65° an with adjustability after installation allowing for a precise fit.







Family of fully adjustable concealed hinges (3/4" - 1 1/2" doors) that can hold up to 200lbs doors..





304B Stainless Steel A robust stainless Steel cup hinge. Adjustable and available for overlay applications..



J95 Heavy Duty Hinge Heavy duty cup hinge available in 2 finishes and optional safety covers (Max weight: 88 lbs/3 hinges).



Lift-Assist Damper (Heavy Duty)


LADH




board

3-5/16" - (84.3 mm)

- Add a smooth soft-close to counter tops in restaurants, bars and reception desks to prevent slamming.
- Lift-Assist feature helps users lift countertop
- Holds door open at 95 degrees.
- Easy installation surface mounted and can be retrofitted
- Stainless steel piano hinge included (see next page for details)
- Can be used in pairs, call our Tech Support for details.







Item No.	Max. Torque per piece (lbs·in)	Panel Thickness	Wt (g)	Box (pcs)	Material	Finish
LADH-35	221 ~ 309	30~50 mm (1-3/16" ~ 2")	2 000	2,000 1	Steel (SPCC)/ Polyacetal (POM)/ABS	Arm: Nickel Chrome Body: Dark Brown or White Other Parts: Nickel Plating
LADH-50	309 ~ 442		2,000			

Folding Bracket With Damper








EB-303/EP-D

- Automatically locks when flap is in open position.
- Press lever to release the lock.
- Hinges not required.
- Damper unit with a soft-closing feature which makes it smoother and safer.
- Durability tested 50,000 cycles (private).
- Refer to the Damper Weight Chart for damper weight capacity.



Item No.	Bracket Load Capacity P1	Bracket Load Capacity P2	Weight (g)	Carton (pcs)	Material
EB-303/EP-D	000 lba	165 lbs	515	20	304
EB-303/EP-D-BL	330 lbs				Stainless Steel

sugatsune.com SUGATSUNE 1.888.557.5267 sugatsune.com SUGATSUNE 1.888.557.5267

Handles

sugatsune.com

	AT 101100	Don't at	Description .
	Image	Product	Description
Wire Pulls		SWP	316 Stainless steel wire pull ideal for harsh and highly corrosive environments, available in various sizes.
Folding Handles	<i>→</i> •.	нк	Stainless steel folding handle available in 3 different sizes.
<u>s</u>	The second second	AT-100	Snap-in type recessed pull. Available in 3 colors.
Recessed Pulls		UT	Stainless steel recessed pull. Available in various sizes.
ŭ		HH-KP150	Stainless steel recessed pull.
		ECH	Stainless steel handle available in 2 sizes
Handles		МТН	Aluminum handle with different length options for various applications. Can be cut to custom fit applications.
Han	ST. ST.	US-70M US-120M US-160M	Rubber grip allows for an easy and comfortable grip, lightweight design. Available in Satin and Mirror finish
		СЈН	Available in 2 sizes and 6 color options that can be used to separate work processes or to warn of dangerous areas.
Knobs		RS-38/S	Lightweight stainless steel knob.
Kn	©	RSS	Lightweight stainless steel knob, available in various sizes and finishes.
Hatch Pull	0.44	ST-90	T-handle designed hatch pull, available in 2 sizes.
Hato		ST-100	Hook-designed hatch pull, available in 2 sizes.

Hooks

	Image	Product	Description
Undermount Hooks	R	RF-50	Stainless steel, 360° rotating undermounted hook.
	To	HJ	Stainless steel undermount hook available in various sizes and finishes.
	T	UJ	Stainless steel, 360° rotating swing hook that features 180° swivel capability that allows this hook to be undermounted.
Swivel Hooks		JF-T	Stainless steel, 180° swivel hook with friction. Ideal for vibration or shock applications and available in 3 different sizes.
Small Hooks	€	FC	Stainless steel small hook; holds up to 26 lbs and available in Titanium.
	-may	TY-30	Stianless Steel wire hook available in various sizes.
Latch Hooks	þþ	EN-K	316 Stainless steel latch hook designed to keep items hooked and can hold up to 132 lbs.
		WH	Stainless steel hook. Keep items hooked, ideal for vibration or shock applications. Available in 2 sizes, 33 lbs load capacity.

Dampers

	Image	Product	Description
Torque Dampers		UDH	Compact designed torque damper, available in various specifications to support torque and application requirements.
Rotary Dampers	*	SRT	Special order one and two-way rotary dampers.
Disk Dampers		UDD	Disc-shaped soft-close damper featuring a narrow profile, excellent for food services environments.
Door Closers	A SE	DC	Surface mounted wood or glass door soft-close catch and door closer.



Unique Convenience



The littlest brother of our LIN-X family is the LIN-X450 designed for cabinet doors. With a space saving concept of the LIN-X Lateral Opening System, it's easy to install, and is also 4-way adjustable to ensure a flush and sleek reveal. Perfect for full acess to under-the-counter space in tight spaces. Single Double Corner **SEE IT IN ACTION**







Sugatsune America 18101 Savarona Way Carson, CA 90746 1-800-562-5267





