

Specialty Magnetic Catches

Sugatsune's wide range of specialty magnetic catches are perfect for maintaining a minimalistic look with maximum strength. The magnetic efficiency of our hardware is suitable for food equipment, medical equipment, manufacturing equipment, clean rooms, and storage carts. Select one of our magnetic catches to add power and durability to your unique applications.



Ultra Thin & Strong Magnetic Catch

MC-159-8



- 3.3 ~ 17.6 lbs magnetic force range
- Max. temperature: 80°C (176°F)
- Steel body
- 3 mm surface thickness

Item No.	Mag. Force (kg)	Weight (g)	Box (pcs)	Carton (pcs)
MC-159-8	8 (17.6 lbs)	14	200	1000

Ultra Thin Stainless Steel Magnetic Catch

MC-159-SUS



- 3.3 ~ 17.6 lbs magnetic force range
- Max. temperature: 80°C (176°F)
- Stainless steel body
- 3 mm surface thickness

Item No.	Mag. Force (kg)	Weight (g)	Box (pcs)	Carton (pcs)
MC-159-SUS	5 (11.0 lbs)	13	200	1000

Sealed Counterplate

MC-JM45



- Hermetically sealed, ideal for high corrosion environments.
- No metal-to-metal contact.
- Ideal for clean-room applications.
- Strong magnetic force.
- Available in two finishes.

Sealed Magnetic Catch

MC-MSH



- Hermetically sealed, ideal for high corrosion environments.
- Sealed with silicon rubber to reduce noise when a door closes.
- No metal-to-metal contact.
- Ideal for clean-room applications.
- Strong magnetic force.

Item No.	Mag. Force (kg)	Weight (g)	Box (pcs)	Carton (pcs)
MC-JMP45WT	3 (6.6 lbs)	8.5	100	1000
MC-JMP45BL	0.0 (0.3	0.0	100	1000

Item No.	Mag. Force (kg)	Weight (g)	Box (pcs)	Carton (pcs)
MC-MSH45BU	2.0 (4.4 lbs)	12	400	4000
MC-MSH50BU	4.0 (8.8 lbs)	15	100	1000





Push-To-Open Door Latch



- Featuring a strong 11 lbs push force.
- Can easily open doors up to 200 lbs.
- Ideal for large doors, up to up to 36" x 96"
- Magnet allows tolerance with 1.5° swivel.
- Passed 100,000 open/close private cycle test.
- Available in two finishes.

Item No.	Mag. Force (kg)	Weight (g)	Max. Door Weight (kg)	Box (pcs)	Carton (pcs)
ML-ZN80WT	0 (0 0)	400	105 (075 !!)	40	40
ML-ZN80BL	3 (6.6 lbs)	160	125 (275 lbs)	10	40



Stainless Steel Magnetic Catch (Ultra-Thin/Back Mount)

MC-159-ST



- No screw heads: easy to install and keep a clean, flat surface.
- Neodymium strength. Ultra thin surface (3 mm thick).
- Stainless steel: high corrosion resistance, suitable for outdoor use.
- Counterplate (MC-159U-ST) is sold separately.

Item No.	Mag. Force (kg)	Weight (g)	Box (pcs)	Carton (pcs)
MC-159-2-ST	2 (4.41 lbs)	44	400	4000
MC-159-4-ST	4 (8.82 lbs)	14	400	1200

Stainless Steel Counter Plate (Back Mount)

MC-159U-ST



Ine bolts are designed to be fixed
with nuts from the back side.

No screw heads.

Item No.	Weight (g)	Box (pcs)	Carton (pcs)
MC-159U-ST	13.2	50	1000





sugatsune.com



America Headquarters 18101 Savarona Way Carson, CA 90746









in

1.888.557.5267