HINGES

THICK DOOR CONCEALED HINGE WITH ADJUSTABLE SOFT-CLOSE

H360-26/C26/D26

5-speed damper power


Installation drawing

adjustment lever



FOR THICK DOORS, With damper function (5 levels), 100° opening

SUGATSUNE



RoHS


- Load capacity: 9 kg (19.8 lbs)/2 pcs, 15 kg (33 lbs)/3 pcs.
- Maximum door width: 600 mm (23-5/8").
 Maximum door thickness: 30 mm (1-3/16")
- Clip on type for easy installation.
- 3-way adjustment with door installed. · Mounting plate sold separately.


Side board Thickness 30

Successfully passed 200,000 cycles test.



Locus chart S=1/1





Clearances for door edge O.C. (A) and hinge side O.C. (B) are necessary. O.C. (A) and (B) change depending on door thickness and bore distance (C). Refer to locus chart and tables below when designing cabinets.

Opening clearance (B), door thickness (D) and bore distance (C) relationship

Door Thickness (D)	Bore Distance (C)						
	3	4	5	6	7	8	
18	0	0	0	0	0	0	
20	0	0	0	0	0	0	
22	0	0	0	0	0	0	
24	0.1	0.1	0.1	0.1	0.1	0.1	
26	0.3	0.3	0.3	0.3	0.3	0.3	
28	1.7	0.7	0.5	0.5	0.5	0.5	
30	3.9	2.9	2.0	1.4	0.8	0.8	
32*	5.9	4.9	3.9	3.3	2.6	2.1	
34*	8.1	7.1	6.1	5.1	4.5	3.9	
	O.C. (B)						

• The table above shows O.C. (B) for C1 chamfering (chamfer plane).

* Please refer to the locus chart if door thickness is over 30mm. O.C. (B) can be made smaller by R chamfering (round chamfer) and C chamfering (chamfer plane) on the door.

Item No	Opening angle	Туре	Material	Finish	Carton
H360-D26-0T		Soft close (5 levels)			
H360-26-0T	93°	Free swinging	Steel	Nickel	100pcs
H360-C26-0T		Self-closing			

Cut out dimensions (wooden doors)

