		SUGATS	UNE		
NON-MAGN	NETIC TOUC	H LATCH		Roms 2.7×13 2.4×10 STEEL	MC-28
		<ul> <li>Push to latch/unlatch.</li> <li>Touch latch with floating strike allows for easy alignment.</li> <li>Note: <ul> <li>For overlay door, allow 3 mm (1/8") gap between door and cabinet frame for push space.</li> <li>Pulling door with excessive force without unlatching the unit may damage the mechanism.</li> <li>Constant loading of over 3 kgf or excessive pushing or pulling is not recommended.</li> </ul> </li> </ul>			
	g Force (kg) Weight (g) .6 lbs) 15	Box (pcs) 50	Carton (pcs) 500	Part NameMaterialBodyABSArmPolyacetaStrikePolyamide	
NON-MAGN		H LATCH			21P/BLK
			bore depth2 (12)(Lock strok (10)(Lock strok (10)(Lock strok (10)(Lock strok (10)(Lock strok (10)(Lock strok (10)(Lock strok (10)(Lock strok (10)(Lock strok (10)(Lock strok	F	Black
	g Force (kg) Weight (g) 22 lbs) 16.3	Box (pcs) 100	Carton (pcs) 800	Image: Second strike     Image: Second strike	
NON-MAGN	Free (5.5) Lock (57/64) 1.5 Lock (57/64) (20) (20) (20) (20) (20) (20) (20) (3) (4) (3) (4) (4) (4) (4) (4) (4) (4) (4) (4) (4	ease stroke		Push to latch/unlatch.     Thin design is ideal for tight sp Snap-in style catch.     Strike/Counterplate not availat	

Recommended Strike Dimension Cut Out Dimensions Installation

**←**7.5 →

Item No.	Retaining Force (kg)	Weight (g)	Box (pcs)	Carton (pcs)	Material	Color
PR-3PK	2.2 (4.8 lbs)	2.5	400	4000	ABS	Black

+7.4+

+ 3.6

**1-800-562-5267** (U.S.A. Only)

## 124

**CATCHES & LATCHES**