

TWIN WHEEL CASTER (PLATE TYPE)






FA-45-PS, P

• Light & durable aluminum body construction.



FA-45-PS
(w/ Brake)

FA-45-P
(w/o Brake)



Item No.	Type	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
FA-45-PS	w/ Brake	50 (110 lbs)	117	4	100
FA-45-P	w/o Brake	50 (110 lbs)	113		

No.	Part Name	Material	Finish
①	Body	Aluminum Alloy	Silver
②	Mounting Plate	Steel	Yellow Zinc Chromate
③	Wheel	Polyamide	Black

TWIN WHEEL CASTER (PLATE TYPE)






FP-45-PS, P

• Caster with high quality polyamide body. Excellent durability, chemical / weather / wear resistance.



FP-45-PS
(w/ Brake)

FP-45-P
(w/o Brake)



Item No.	Type	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
FP-45-PS	w/ Brake	40 (88 lbs)	98	4	100
FP-45-P	w/o Brake	40 (88 lbs)	94		

No.	Part Name	Material	Finish
①	Body	Polyamide	Black
②	Mounting Plate	Steel	Yellow Zinc Chromate
③	Wheel	Polyamide	Black