

SLIDING POCKET DOOR SYSTEM (Recessed Mount) **FD80DHCHP-PD**




SLIDING & FOLDING DOOR HARDWARE



Door Weight	Max. 176 lbs (80 kg)
Door Thickness (Min.)	Recessed: 1-5/16" (34 mm), Surface: 1-3/16" (30 mm)
Door Width	30-7/8" ~ 59-1/16" (784-1500 mm) [98-7/16" (2500 mm) or less in height] 33-7/16" ~ 59-1/16" (850-1500 mm) [98 7/16" ~ 106-5/16 (2501-2700 mm) in height]
Door Height	Max. 106-5/16" (2700 mm)









- Easy installation and maintenance
 - Built in soft-close and soft-open damper.
 - Two-rail system, allows all components to be fixed or adjusted through the opening without breaking the pocket (Sold Separately).
 - Use with removable jam/trim/casing.
 - For interior use only.
 - Rollers are recess mounted to top of door.
 - High durability, passed 200,000 cycle test (private)
- NOTE:** Pocket Door Retail Kit (FD80PD-RM2-RT) includes hardware and 2160 mm track.


Door Installation



Parts Set (Per Door)		Necessary Parts
Item Code	Item Name	Description
250-029-771	FD80DHCHP-PD	Recessed Roller Two-Way Soft Close


Parts Included

No.	Qty	Part Name	Dimensions	Description
1	1 pc	Recessed Mount Roller Two-Way Soft Close		<p>Item Name: FD80-WRH-DSC</p> <ul style="list-style-type: none"> Material: Zinc Alloy (ZDC) / Polyacetal (POM) Finish / Colour: Nickel / Black <p>Remarks: Do not use the included trigger.</p>
2	1 pc	Front Trigger		<p>Item Name: FD80-TRGPF</p> <ul style="list-style-type: none"> Material: 304 Stainless Steel Finish: Plain
3	1 pc	Pocket Trigger		<p>Item Name: FD80-TRGPB-MB</p> <ul style="list-style-type: none"> Material: 304 Stainless Steel Finish: Plain
4	1 pc	Recessed Roller		<p>Item Name: FD80-WRH</p> <ul style="list-style-type: none"> Material: Zinc Alloy (ZDC) / Polyacetal (POM) Finish / Colour: Nickel / Natural
5	2 pcs	Hanging Bracket (160 mm)		<p>Item Name: FD70B-HB160</p> <ul style="list-style-type: none"> Material: Aluminium Alloy Finish: Anodized Silver Screw: Pan Head Tapping Screw 5x40
6	2 pcs	End Cap		<p>Item Code: 250-121-142 Item Name: FD70B-EC-BL</p> <ul style="list-style-type: none"> Material: Elastomer (TPE) Colour: Black
7	1 pc	Floor Guide		<p>Item Name: FD50-BGR18</p> <ul style="list-style-type: none"> Material: 430 Stainless Steel/ Polyacetal (POM) Finish / Colour: Polished / Natural Screw: Raised Countersunk Head Tapping Screw 3.5x30
8	1 pc	Bottom Guide Rail (1500 mm)		<p>Item Name: FD30-HBRT1500SIL</p> <ul style="list-style-type: none"> Material: Aluminium Alloy Finish: Anodized Silver

Upper Track		Necessary Parts			
No.	Length	Item Code	Part Name	Dimensions	Desc.
9	1260 mm	FD80-TRP1260-SL	Upper Track		<ul style="list-style-type: none"> Material: Aluminium Alloy Finish: Anodized Silver
10	2160 mm	FD80-TRP2160-SL			
11	2760 mm	FD80-TRP2760-SL			
12	3960 mm	FD80-TRP3960-SL			

Hole Dimensions of Upper Track

In case of 1260 mm



In case of 2160 mm, 2760 mm & 3960 mm

