



STAINLESS STEEL LONG-STEM LEVELING GLIDE



MKPLS



- Double structure of cover/bolt and base allow easy height adjustment without lifting the leg.
- Swivels approximately 10° to compensate for uneven floors.
- 304 stainless steel construction is ideal for humid environments or application where corrosion is an issue.




Part Name	Material	Finish
Body	304 Stainless Steel	Satin
Cover		Plain
Base		

Item No.	M	D	d	H	h	S	B	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
MKPLS-32/10/80	M10x1.5	32 (1-17/64")	27	96 (3-25/32")	10.5	80.0	17	200 (440 lbs)	79	30	240
MKPLS-40/12/80	M12x1.75	40 (1-37/64")	34	97 (3-13/16")	11.5			300 (660 lbs)	125		
MKPLS-50/12/80		50 (1-31/32")	44	100 (3-15/16")		78.5	24	340 (748 lbs)	150	20	160
MKPLS-50/16/78	M16x2.0									320 (704 lbs)	220


STAINLESS STEEL LONG-STEM LEVELING GLIDE



MKRLS



- Double structure of cover/bolt and base allow easy height adjustment without lifting the leg.
- Swivels approximately 10° to compensate for uneven floors.
- Leveling glide with elastomer base to prevent skidding.



Part Name	Material	Finish
Body	304 Stainless Steel	Satin
Base	Elastomer	Black

Item No.	M	D	d	H	h	S	B	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
MKRLS-32/10/80	M10x1.5	32 (1-17/64")	27	96 (3-25/32")	11	80.0	17	80 (176 lbs)	76	30	240
MKRLS-40/12/80	M12x1.75	40 (1-37/64")	34	97 (3-13/16")	11.5			100 (220 lbs)	140		
MKRLS-50/12/80		50 (1-31/32")	44	100 (3-15/16")		78.5	24	80 (176 lbs)	215	15	120
MKRLS-50/16/78	M16x2.0										