


MAGNETIC CATCH (RUBBER ROLL TYPE)



KMS




- Easy to cut length.
- Easy to apply with glue.
- Note: 1) Not for use in applications with high temperature (80°C/176°F) or humidity.
2) Do not use to secure/support heavy objects.

| Item No. | W | t | Magnetic Force (kg) | Weight (g) | Box (pcs) |
|------------|------|-----|------------------------------------|------------|-----------|
| KMS-1-1000 | 13.0 | 0.8 | 0.06 tkg/cm ² (0.85psi) | 37 | 1 |
| KMS-2-1000 | 19.1 | | | 54 | |
| KMS-3-1000 | 25.4 | | | 77 | |
| KMS-4-1000 | 12.7 | | | 66 | |
| KMS-5-1000 | 19.1 | 1.5 | 0.09 tkg/cm ² (1.28psi) | 100 | |
| KMS-6-1000 | 25.4 | | | 140 | |

MAGNETIC CATCH



MC-SM10




| No. | Part Name | Material | Finish |
|-----|--------------|----------|----------|
| ① | Body | Aluminum | Anodized |
| ② | Yoke | Steel | Chromate |
| ③ | Magnet | Ferrite | - |
| ④ | Counterplate | Steel | Chromate |

| Item No. | Magnetic Force (kg) | Weight (g) | Box (pcs) | Carton (pcs) |
|----------|---------------------|------------|-----------|--------------|
| MC-SM10 | 2.0 (4.4 lbs) | 12 | 100 | 1600 |

MAGNETIC CATCH



MC0750



- Low profile design is ideal for tight spaces.

| No. | Part Name | Material | Finish |
|-----|-----------|---------------------|----------|
| ① | Yoke | Steel | Nickel |
| ② | Magnet | Ferrite | - |
| ③ | Cover | 304 Stainless Steel | Polished |

| Item No. | Magnetic Force (kg) | Weight (g) | Box (pcs) | Carton (pcs) |
|----------|---------------------|------------|-----------|--------------|
| MC0750 | 2.5 (5.5 lbs) | 19 | 150 | 750 |