


180SUS-C/D46-0T



Applicable gap range: 0–4 mm (with 5 mm bore distance)

Bore Distance (C)	3	4	5
Overlay (E)	3	2	1

For standard type mounting plate 0 mm thickness. Turning the adjustment screw increases the Gap (b) by up to 3 mm. The hinge-side O.C. (B) setting is shown in the table below.

Clearances for door edge O.C. (A) and hinge side O.C. (B) are necessary. O.C. (A) and (B) change depending on door thickness and bore distance (C). Refer to locus chart and tables below when designing cabinets.

Door Thickness (D)	Bore Distance (C)		
	3	4	5
9/16" (15 mm)	0.2	0.2	0.2
5/8" (16 mm)	0.3	0.3	0.3
11/16" (17 mm)	0.4	0.4	0.4
11/16" (18 mm)	0.7	0.6	0.6
3/4" (19 mm)	0.9	0.9	0.8
13/16" (20 mm)	1.2	1.2	1.1
13/16" (21 mm)*	1.7	1.6	1.5
7/8" (22 mm)*	2.3	2.0	1.9
	O.C. (B)		

*Please refer to the locus chart if door thickness is over 20 mm. (O.C. (B) can be reduced by machining the R and C faces on the door.)

Door Thickness (D)	Door Width				
	11-13/16" (300)	15-3/4" (400)	17-3/4" (450)	19-11/16" (500)	23-5/8" (600)
13/16" (20 mm)	0.24	0.18	0.15	0.14	0.12

*Reference values for door widths 500 and 600.

Technical drawing of a door with a circular window. The drawing shows the door's profile and the window's dimensions. Key dimensions include:

- Door height: 2'-7 1/8" (62.5 mm)
- Door width: 1'-3/4" (45 mm)
- Window diameter: 1'-3 3/8" (65 mm)
- Window depth: 1/2" (12 mm)
- Bore Distance (C)
- Front edge
- Bore Distance (C)

Material	Finish
304 Stainless Steel	Polished

Mounting Plate (sold separately) is required for installation. Please order separately.

1-800-562-5267
(U.S.A. Only)