



CONCEALED HINGE (3/4" (19 mm) OVERLAY)



304B-46/19, C46/19



Bore Dimensions

■ Door edge to bore edge distance (C) and Overlay distance (B) Table 1.

Door edge to bore edge distance (C)	1/8" (3 mm)	3/16" (4 mm)	3/16" (5 mm)
Overlay distance (B)	11/16" (17 mm)	11/16" (18 mm)	3/4" (19 mm)

■ Hinge side opening clearance chart Table 2.

Door thickness (D)	Door edge to bore edge distance (C)		
	1/8" (3 mm)	3/16" (4 mm)	3/16" (5 mm)
9/16" (15 mm)	0.5	0.5	0.5
5/8" (16 mm)	0.7	0.7	0.7
11/16" (17 mm)	0.8	0.8	0.8
11/16" (18 mm)	1.0	1.0	1.0
3/4" (19 mm)	1.2	1.2	1.2
13/16" (20 mm)	1.4	1.4	1.4

Hinge side O.C. (A)

Item No.	Type	Weight (g)	Carton (pcs)
304B-46/19	Free Swinging	60	200
304B-C46/19	Self-Closing		



*Mounting Plate sold separately. See P.297

Material	Finish
304 Stainless Steel	Polished

CONCEALED HINGE (9/16" (14 mm) OVERLAY)



304B-46/14, C46/14



Bore Dimensions

■ Door edge to bore edge distance (C) and Overlay distance (B) Table 1.

Door edge to bore edge distance (C)	1/8" (3 mm)	3/16" (4 mm)	3/16" (5 mm)
Overlay distance (B)	1/2" (12 mm)	1/2" (13 mm)	9/16" (14 mm)

■ Hinge side opening clearance chart Table 2.

Door thickness (D)	Door edge to bore edge distance (C)		
	1/8" (3 mm)	3/16" (4 mm)	3/16" (5 mm)
9/16" (15 mm)	0.5	0.5	0.5
5/8" (16 mm)	0.7	0.7	0.7
11/16" (17 mm)	0.8	0.8	0.8
11/16" (18 mm)	1.0	1.0	1.0
3/4" (19 mm)	1.2	1.2	1.2
13/16" (20 mm)	1.4	1.4	1.4

Hinge side O.C. (A)

Item No.	Type	Weight (g)	Carton (pcs)
304B-46/14	Free Swinging	60	200
304B-C46/14	Self-Closing		

*Mounting Plate sold separately. See P.297

Material	Finish
304 Stainless Steel	Polished