

SPRING HINGE



JSA

HINGES




JSA-120A




JSA-180S



- Spring loaded for self closing.
- Adjustable spring tension.
- Successfully passed 500,000 open/close private cycle tests.




JSA-120




JSA-180


Installation



Adjustable Spring Tension



Self Closing



Item No.	D	t	d ₁	d ₂	Load Capacity		Weight (g)	Box (pcs)	Carton (pcs)	Material	Finish
					2 Hinges	3 Hinges					
JSA-120A	5/8" (16)	3/16" (4.0)	3/16" (5.0)	5/16" (8)	44 lbs (20 kg)	66 lbs (30 kg)	175	2	20	Aluminum	Anodized
JSA-180A	11/16" (17)	1/8" (2.5)	1/4" (5.5)	3/8" (9)	44 lbs (20 kg)	66 lbs (30 kg)	260				
JSA-120S	11/16" (17)	1/8" (2.5)	1/4" (5.5)	3/8" (9)	44 lbs (20 kg)	66 lbs (30 kg)	303	2	20	304 Stainless Steel	Satin
JSA-180S	11/16" (18)	1/8" (3.0)	1/4" (5.5)	3/8" (9)	44 lbs (20 kg)	66 lbs (30 kg)	526				

SPRING HINGES

SPRING HINGE




JST-150S




JST-150S




- Spring loaded for self closing.
- Adjustable spring tension.
- Successfully passed 500,000 open/close private cycle tests.




Installation



Adjustable Spring Tension



Self Closing



Item No.	Load capacity		Weight (g)	Box (pcs)	Carton (pcs)
	2 Hinges	3 Hinges			
JST-150S	88 lbs (40 kg)	132 lbs (60 kg)	336	2	20

Material	Finish
304 Stainless Steel	Satin