

ADJUSTABLE SOFT-DOWN STAY







NSDX-35

LID SUPPORTS

ADJUSTABLE SOFT-DOWN STAYS



- For UPWARD-OPENING FLAP DOOR used with piano, butt or concealed hinges.
- Opening angle 80°, 90° or 100°.
- NSDX-35 is designed to hold door in fully opened position.
- Speed adjustment screw located on front for easy adjustment.
- Two stop version (holds door at 65° and 90°) is also available.
- Torque Calculation :
Torque = Door Height × 0.5 × Door Weight
Per Piece: 19~60 lbs-inch (20~70 kg-cm)
Per Pair: 38~120 lbs-inch (40~140 kg-cm)



Material		Finish		
Zinc Alloy		Nickel		
Steel				
Item No.	Weight (g)	Box (pcs)	Carton (pcs)	
NSDX-35RK	Right	181	20	80
NSDX-35LK	Left			

Opening Angle	Hinge Type	A	B	C	D	E	F
80°	Concealed Hinge	4-3/16" (106)	4-1/8" (105)-S	4-3/4" (121)-S	-	-	7/16" (11)
	Piano/Butt Hinge	3-15/16" (100)	-	-	3-7/8" (99)	4-1/2" (115)	
90°	Concealed Hinge	3-7/8" (98)	3-13/16" (97)-S	4-7/16" (113)-S	-	-	
	Piano/Butt Hinge	3-5/8" (91.5)	-	-	3-9/16" (90.5)	4-3/16" (106.5)	
100°	Concealed Hinge	3-5/8" (92.5)	3-5/7" (91.5)-S	4-1/4" (107.5)-S	-	-	
	Piano/Butt Hinge	3-3/8" (85)	-	-	3-5/16" (84 mm)	3-15/16" (100)	

() units in mm