

EXTENSION HANGER



LOAD CAPACITY
3 kg
6.6 lbs

TEST 5
P.696

4x25
STAINLESS

UH SERIES

- Space-saving, undermount design for narrow spaces.
- Includes 1" (M4 × 25) long screws.



Part Name	Material	Finish/Color
Hanger Rod	304 Stainless Steel	Chrome/Black
Rod Retainer	Steel	
End Cap	Plastic	

Item No.	L ₁	L ₂	L ₃	C	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
UH-300	19-21/64" (491)	11-13/16" (300)	10-13/16" (274)	10-25/64" (264)	6.6 lbs (3 kg)	365	5	30
UH-350	22-31/64" (571)	13-3/4" (350)	12-3/4" (324)	12-23/64" (314)		440		
UH-400	25-1/32" (636)	15-3/4" (400)	14-3/4" (374)	14-21/64" (364)		505		
UH-450	28-25/64" (721)	17-3/4" (450)	16-11/16" (424)	16-19/64" (414)		570		

EXTENSION HANGER



LOAD CAPACITY
4-6 kg
8.8-13.2 lbs

TEST 5
P.696

3.5x20
STEEL

W SERIES

- Space-saving, undermount design for narrow spaces.
- Molded nylon finger grip for easy accessibility.
- Includes 3/4" (M3.5 × 20) long screws.



Part Name	Material	Finish/Color
Hanger Rod	Steel	Nickel/Black
Retainer Guide	Nylon	

Item No.	L ₁	L ₂	H	C	Load Capacity	Weight (g)	Box (pcs)	Carton (pcs)
W-300	19-39/64" (498)	11-13/16" (300)	2-7/8" (73)	10-3/4" (273)	13.2 lbs (6 kg)	485	5	30
W-350	21-57/64" (556)	13-3/4" (350)		12-3/4" (323)	11 lbs (5 kg)	560		
W-400	24-23/32" (628)	15-3/4" (400)		14-11/16" (373)	11 lbs (5 kg)	630		
W-450	27-31/64" (698)	17-3/4" (450)		16-5/8" (423)	8.8 lbs (4 kg)	715		