


LOW PROFILE HEAVY DUTY CASTER



HR



- Low profile and heavy duty up to 255 kg (561 lbs), ideal for manufacturing equipment.
- Hardened frame for maximum rigidity and strength.
- Hexavalent chromium free. Using trivalent chromium for RoHS compliance.
- Two wheel types:
 - Phenolic
 - Reinforced Nylon with ball bearing spindle

Part Name	Material	Finish
Body	Steel	Clear Zinc Chromate (Trivalent Chromium)
Mounting Plate		
Wheel	Reinforced Nylon(GNB)	Black
	Phenolic Resin(PB)	

Item No.	Bearing in wheels	D	Wheel Width	H	A	B	X	Y	P	Load Capacity (kg)	Weight (g)	Box (pcs)	Carton (pcs)
HR-50GNB	Without Bearing	50	28	68	80	50	66	36	6.5	163 (359 lbs)	200	36	600
HR-65PB	With Bearing	65	38	92	111	67	91	47	10.5	234 (516 lbs)	615	12	120
HR-75PB		75	38	106	123	72	103	52	10.5	255 (561 lbs)	725	12	120

CASTER COMBINATION – SET UP

Better



Cost	Stability	Control	Load Capacity
A	B / C	A / B	E
B / C / D	D / E	D / E	B / C / D
E	A	C	A

A: TYPE - 3 x Swivel
SET UP - 2 + 1 Triangle

B: TYPE - 4 x Swivel
SET UP - Square

C: TYPE - 2 x Swivel & 2 x Fix
SET UP - Square

D: TYPE - 2 x Swivel & 2 x Fix
SET UP - Rhombus

E: TYPE - 4 x Swivel & 2 x Fix (Middle)
SET UP - Square

